

PANASONIC SEMICONDUCTOR Diodes



This product is RoHS compliant.

ZENER DIODES (CONT.)

For quantities greater than listed, call for quote.

MOUSER STOCK NO.		Package	VZ (V) Nom.	IR (Max) (µA)	PD (Max) (mW)	Price Each		
Mfr.	Mfr. Part No.					1	25	100
667	DZ3S062D0L	SSMini3-F3-B	6.2	0.2	150	.17	.169	.165
667	DZ3X062D0L	Mini3-G3-B	6.2	0.2	200	.25	.231	.225
667	DZ4J062K0R	SMini4-F3-B	6.2	0.2	200	.15	.11	.107
667	DZ5S062D0R	SSMini5-F4-B	6.2	0.2	150	.39	.388	.378
667	DZ2406200L	TMiniP2-F2-B	6.2	10	2000	.42	.323	.294
667	DZ2W06200L	Mini2-F3-B	6.2	10	1000	.32	.249	.226
667	DZ2706800L	SSSMini2-F4-B	6.8	0.1	120	.25	.222	.216
667	DZ2J06800L	SMini2-F5-B	6.8	0.1	200	.15	.107	.104
667	DZ2J068M0L	SMini2-F5-B	6.8	0.1	200	.15	.107	.104
667	DZ2S06800L	SSMini2-F5-B	6.8	0.1	150	.15	.134	.131
667	DZ2S068M0L	SSMini2-F5-B	6.8	0.1	150	.15	.134	.131
667	DZ3S068D0L	SSMini3-F3-B	6.8	0.1	150	.17	.169	.165
667	DZ3X068D0L	Mini3-G3-B	6.8	0.1	200	.25	.231	.225
667	DZ4J068K0R	SMini4-F3-B	6.8	0.1	200	.15	.11	.107
667	DZ5S068D0R	SSMini5-F4-B	6.8	0.1	150	.39	.388	.378
667	DZ37068D0L	SSSMini3-F2-B	6.8	-	150	.34	.333	.324
667	DZ6J068S0R	SMini6-F3-B	6.8	-	150	.15	.122	.118
667	DZ2406800L	TMiniP2-F2-B	6.8	10	2000	.42	.323	.294
667	DZ2W06800L	Mini2-F3-B	6.8	10	1000	.32	.249	.226
667	DZ2707500L	SSSMini2-F4-B	7.5	0.1	120	.16	.157	.153
667	DZ2J07500L	SMini2-F5-B	7.5	0.1	200	.15	.107	.104
667	DZ2J075M0L	SMini2-F5-B	7.5	0.1	200	.15	.107	.104
667	DZ4J075K0R	SMini4-F3-B	7.5	0.1	200	.15	.107	.104
667	DZ2407500L	TMiniP2-F2-B	7.5	10	2000	.42	.323	.294
667	DZ2W07500L	Mini2-F3-B	7.5	10	1000	.32	.249	.226
667	DZ2708200L	SSSMini2-F4-B	8.2	0.1	120	.16	.157	.153
667	DZ2J08200L	SMini2-F5-B	8.2	0.1	200	.15	.107	.104
667	DZ2J082M0L	SMini2-F5-B	8.2	0.1	200	.15	.107	.104
667	DZ2S08200L	SSMini2-F5-B	8.2	0.1	150	.15	.134	.131
667	DZ3S082D0L	SSMini3-F3-B	8.2	0.1	150	.17	.169	.165
667	DZ5S082D0R	SSMini5-F4-B	8.2	0.1	150	.39	.388	.378
667	DZ37082D0L	SSSMini3-F2-B	8.2	-	150	.22	.215	.21
667	DZ2408200L	TMiniP2-F2-B	8.2	10	2000	.42	.323	.294
667	DZ2W08200L	Mini2-F3-B	8.2	10	1000	.32	.249	.226
667	DZ2709100L	SSSMini2-F4-B	9.1	0.1	120	.16	.157	.153
667	DZ2J09100L	SMini2-F5-B	9.1	0.1	200	.15	.107	.104
667	DZ2J091M0L	SMini2-F5-B	9.1	0.1	200	.15	.107	.104
667	DZ2S09100L	SSMini2-F5-B	9.1	0.1	150	.15	.134	.131
667	DZ2S091M0L	SSMini2-F5-B	9.1	0.1	150	.15	.134	.131
667	DZ4J091K0R	SMini4-F3-B	9.1	0.1	200	.15	.107	.104
667	DZ2409100L	TMiniP2-F2-B	9.1	10	2000	.42	.323	.294
667	DZ2W09100L	Mini2-F3-B	9.1	10	1000	.32	.249	.226
667	DZ2710000L	SSSMini2-F4-B	10	0.05	120	.25	.222	.216
667	DZ2J10000L	SMini2-F5-B	10	0.05	200	.15	.107	.104
667	DZ2J100M0L	SMini2-F5-B	10	0.05	200	.15	.107	.104
667	DZ2S10000L	SSMini2-F5-B	10	0.05	150	.15	.134	.131
667	DZ2S100M0L	SSMini2-F5-B	10	0.05	150	.15	.134	.131
667	DZ37100D0L	SSSMini3-F2-B	10	0.05	150	.09	.076	.074
667	DZ3S100D0L	SSMini3-F3-B	10	0.05	150	.17	.169	.165
667	DZ4J100K0R	SMini4-F3-B	10	0.05	200	.15	.11	.107
667	DZ5S100D0R	SSMini5-F4-B	10	0.05	150	.39	.388	.378
667	DZ2410000L	TMiniP2-F2-B	10	10	2000	.42	.323	.294
667	DZ2W10000L	Mini2-F3-B	10	10	1000	.32	.249	.226
667	DZ2711000L	SSSMini2-F4-B	11	0.05	120	.16	.157	.153
667	DZ2J11000L	SMini2-F5-B	11	0.05	200	.15	.107	.104
667	DZ2J110M0L	SMini2-F5-B	11	0.05	200	.15	.107	.104
667	DZ2S11000L	SSMini2-F5-B	11	0.05	150	.15	.134	.131
667	DZ2S110M0L	SSMini2-F5-B	11	0.05	150	.15	.134	.131
667	DZ24110K0R	SMini4-F3-B	11	0.05	200	.15	.107	.104
667	DZ2712000L	SSSMini2-F4-B	12	0.05	120	.25	.222	.216
667	DZ2J12000L	SMini2-F5-B	12	0.05	200	.15	.107	.104
667	DZ2J120M0L	SMini2-F5-B	12	0.05	200	.15	.107	.104
667	DZ2S12000L	SSMini2-F5-B	12	0.05	150	.15	.134	.131
667	DZ2S120M0L	SSMini2-F5-B	12	0.05	150	.15	.134	.131
667	DZ37120D0L	SSSMini3-F2-B	12	0.05	150	.09	.076	.074
667	DZ3S120D0L	SSMini3-F3-B	12	0.05	150	.08	.078	.076
667	DZ5S120D0R	SSMini5-F4-B	12	0.05	150	.39	.388	.378
667	DZ2412000L	TMiniP2-F2-B	12	10	2000	.42	.323	.294
667	DZ2W12000L	Mini2-F3-B	12	10	1000	.32	.249	.226
667	DZ2413000L	TMiniP2-F2-B	13	10	2000	.42	.323	.294
667	DZ2W13000L	Mini2-F3-B	13	10	1000	.32	.249	.226
667	DZ2J13000L	SMini2-F5-B	13	0.05	200	.15	.107	.104
667	DZ2J130M0L	SMini2-F5-B	13	0.05	200	.15	.107	.104
667	DZ2S13000L	SSMini2-F5-B	13	0.05	150	.15	.134	.131
667	DZ2S130M0L	SSMini2-F5-B	13	0.05	150	.15	.134	.131
667	DZ4J130K0R	SMini4-F3-B	13	0.05	200	.15	.107	.104

For quantities greater than listed, call for quote.

MOUSER STOCK NO.		Package	VZ (V) Nom.	IR (Max) (µA)	PD (Max) (mW)	Price Each		
Mfr.	Mfr. Part No.					1	25	100
667	DZ2J14000L	SMini2-F5-B	14	0.05	200	.15	.107	.104
667	DZ2J140M0L	SMini2-F5-B	14	0.05	200	.15	.107	.104
667	DZ2J15000L	SMini2-F5-B	15	0.05	200	.15	.107	.104
667	DZ2J150M0L	SMini2-F5-B	15	0.05	200	.15	.107	.104
667	DZ2S15000L	SSMini2-F5-B	15	0.05	150	.15	.134	.131
667	DZ2S150M0L	SSMini2-F5-B	15	0.05	150	.15	.134	.131
667	DZ4J150K0R	SMini4-F3-B	15	0.05	200	.15	.11	.107
667	DZ2416000L	TMiniP2-F2-B	15	10	2000	.42	.323	.294
667	DZ2W16000L	Mini2-F3-B	15	10	1000	.32	.249	.226
667	DZ2416000L	TMiniP2-F2-B	16	10	2000	.42	.323	.294
667	DZ2W16000L	Mini2-F3-B	16	10	1000	.32	.249	.226
667	DZ2716000L	SSSMini2-F4-B	16	0.05	120	.16	.157	.153
667	DZ2J16000L	SMini2-F5-B	16	0.05	200	.15	.107	.104
667	DZ2J160M0L	SMini2-F5-B	16	0.05	200	.15	.107	.104
667	DZ2S16000L	SSMini2-F5-B	16	0.05	150	.15	.134	.131
667	DZ2S160M0L	SSMini2-F5-B	16	0.05	150	.15	.134	.131
667	DZ2718000L	SSSMini2-F4-B	18	0.05	120	.16	.157	.153
667	DZ2J18000L	SMini2-F5-B	18	0.05	200	.15	.107	.104
667	DZ2J180M0L	SMini2-F5-B	18	0.05	200	.15	.107	.104
667	DZ2S18000L	SSMini2-F5-B	18	0.05	150	.15	.134	.131
667	DZ2S180M0L	SSMini2-F5-B	18	0.05	150	.15	.134	.131
667	DZ4J180K0R	SMini4-F3-B	18	0.05	200	.15	.11	.107
667	DZ2418000L	TMiniP2-F2-B	18	10	2000	.42	.323	.294
667	DZ2W18000L	Mini2-F3-B	18	10	1000	.32	.249	.226
667	DZ2720000L	SSSMini2-F4-B	20	0.05	120	.16	.157	.153
667	DZ2J20000L	SMini2-F5-B	20	0.05	200	.15	.107	.104
667	DZ2J200M0L	SMini2-F5-B	20	0.05	200	.15	.107	.104
667	DZ2S20000L	SSMini2-F5-B	20	0.5	150	.15	.134	.131
667	DZ2S200M0L	SSMini2-F5-B	20	0.5	150	.15	.134	.131
667	DZ2420000L	TMiniP2-F2-B	20	10	2000	.42	.323	.294
667	DZ2W20000L	Mini2-F3-B	20	10	1000	.32	.249	.226
667	DZ2J22000L	SMini2-F5-B	22	0.05	200	.15	.107	.104
667	DZ2J220M0L	SMini2-F5-B	22	0.05	200	.15	.107	.104
667	DZ2S220M0L	SSMini2-F5-B	22	0.05	150	.15	.134	.131
667	DZ2422000L	TMiniP2-F2-B	22	10	2000	.42	.323	.294
667	DZ2W22000L	Mini2-F3-B	22	10	1000	.32	.249	.226
667	DZ2724000L	SSSMini2-F4-B	24	0.05	120	.16	.157	.153
667	DZ2J24000L	SMini2-F5-B	24	0.05	200	.15	.107	.104
667	DZ2J240M0L	SMini2-F5-B	24	0.05	200	.15	.107	.104
667	DZ2424000L	TMiniP2-F2-B	24	10	2000	.42	.323	.294
667	DZ2W24000L	Mini2-F3-B	24	10	1000	.32	.249	.226
667	DZ2J27000L	SMini2-F5-B	27	0.05	200	.15	.107	.104
667	DZ2J270M0L	SMini2-F5-B	27	0.05	200	.15	.107	.104
667	DZ2427000L	TMiniP2-F2-B	27	10	2000	.42	.323	.294
667	DZ2W27000L	Mini2-F3-B	27	10	1000	.32	.249	.226
667	DZ2730000L	SSSMini2-F4-B	30	0.05	120	.16	.157	.153
667	DZ2J30000L	SMini2-F5-B	30	0.05	200	.10	.095	.092
667	DZ2J300M0L	SMini2-F5-B	30	0.05	200	.10	.095	.092
667	DZ2S30000L	SSMini2-F5-B	30	0.05	150	.15	.134	.131
667	DZ2S300M0L	SSMini2-F5-B	30	0.05	150	.15	.134	.131
667	DZ2430000L	TMiniP2-F2-B	30	10	2000	.42	.323	.294
667	DZ2W30000L	Mini2-F3-B	30	10	1000	.32	.249	.226
667	DZ2J33000L	SMini2-F5-B	33	0.05	200	.15	.107	.104
667	DZ2J330M0L	SMini2-F5-B	33	0.05	200	.15	.107	.104
667	DZ2S33000L	SSMini2-F5-B	33	0.05	150	.15	.134	.131
667	DZ2S330M0L	SSMini2-F5-B	33	0.05	150	.15	.134	.131
667	DZ4J330K0R	SMini4-F3-B	33	0.05	200	.15	.107	.104
667	DZ2433000L	TMiniP2-F2-B	33	10	2000	.42	.323	.294
667	DZ2W33000L	Mini2-F3-B	33	10	1000	.32	.249	.226
667	DZ2J36000L	SMini2-F5-B	36	0.05	200	.15	.107	.104
667	DZ2J360M0L	SMini2-F5-B	36	0.05	200	.15	.107	.104
667	DZ2436000L	TMiniP2-F2-B	36	5	2000	.42	.323</	