

TOSHIBA Diodes

TOSHIBA
Leading Innovation >>>

TOSHIBA SCHOTTKY BARRIER DIODES

RoHS Compliant This product is RoHS compliant.



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Voltage Output	Current	Price Each			
					1	10	100	250
757-1SS315TPH3F	1SS315TPH3F	USC-2	5V	30mA	.16	.128	.109	.10
757-1SS405(TPH3,F)	1SS405(TPH3,F)	ESC-2	20V	50mA	.09	.07	.06	.055
757-CRS06(TE85L,Q,M)	CRS06(TE85L,Q,M)	S-FLAT-2	20V	1A	.22	.187	.159	.145
757-DSR01S30SCTPL3	DSR01S30SC(TPL3)	SC-2	30V	100mA	.14	.12	.104	.084
757-1SS416CT(TPL3)	1SS416CT(TPL3)	US-6	30V	100mA	.14	.11	.094	.086
757-1SS420(TPL3,F)	1SS420(TPL3,F)	ESC-2	30V	200mA	.08	.063	.058	.051
757-1SS424TPL3F	1SS424(TPL3,F)	ESC-2	30V	200mA	.09	.07	.06	.055
757-CES520L3F	CE520L3F	SOD-523	30V	1A	.11	.09	.078	.063
757-CES521L3F	CE521L3F	SOD-523	30V	1A	.11	.09	.078	.063
757-CMS08TE12LQM	CMS08(TE12L,Q,M)	M-FLAT-2	30V	1A	.23	.19	.18	.18
757-CRS01(TE85L,Q,M)	CRS01(TE85L,Q,M)	S-FLAT-2	30V	1A	.19	.155	.132	.12
757-CRS02(TE85L,Q)	CRS02(TE85L,Q)	S-FLAT-2	30V	1A	.21	.173	.148	.132
757-CRS03(TE85L,Q)	CRS03(TE85L,Q)	S-FLAT-2	30V	1A	.20	.156	.133	.121
757-CRS03(TE85L,Q,M)	CRS03(TE85L,Q,M)	S-FLAT-2	30V	1A	.16	.13	.11	.10
757-CRS05(TE85L,Q,M)	CRS05(TE85L,Q,M)	S-FLAT-2	30V	1A	.22	.18	.159	.145
757-CUS02(TE85L,Q)	CUS02(TE85L,Q)	US-FLAT-2	30V	1A	.17	.138	.117	.107
757-CRS08TE85LQM	CRS08(TE85L,Q)	S-FLAT-2	30V	1.5A	.22	.174	.149	.132
757-CRS09(TE85L,Q,M)	CRS09(TE85L,Q,M)	S-FLAT-2	30V	1.5A	.21	.172	.148	.131
757-CMS06TE12L,Q,M	CMS06(TE12L,Q,M)	M-FLAT-2	30V	2A	.30	.24	.206	.182
757-DSF01S30SCTPL3	DSF01S30SC(TPL3)	SC-2	30V	2A	.14	.12	.104	.084
757-CMS01TE12L,Q,M	CMS01(TE12L,Q,M)	M-FLAT-2	30V	3A	.43	.34	.294	.256
757-CMS04TE12L,Q,M	CMS04(TE12L,Q,M)	M-FLAT-2	30V	5A	.50	.405	.347	.306
757-CUS51V30H3F	CUS51V30H3F	SOD-323	30V	5A	.18	.15	.13	.105
757-CRS04(TE85L,Q,M)	CRS04(TE85L,Q,M)	S-FLAT-2	40V	1A	.27	.206	.161	.144
757-CMS11TE12L,Q,M	CMS11(TE12L,Q,M)	M-FLAT-2	40V	2A	.33	.264	.231	.198
757-1SS294TE85LF	1SS294(TE85L,F)	S-MINI-3	45V	100mA	.15	.12	.112	.107
757-1SS393SULF	1SS393SU,LF	SC-70	45V	1A	.18	.15	.13	.105
757-CES388L3F	CE388L3F	SOD-523	45V	1A	.11	.09	.078	.063
757-1SS294SLF	1SS294SLF	SC-59	45V	2A	.10	.09	.08	.074
757-CUS04(TE85L,Q)	CUS04(TE85L,Q)	US-FLAT-2	60V	0.7A	.16	.132	.112	.102

TOSHIBA SWITCHING DIODES



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Voltage Output	Average Current	Price Each			
					1	10	100	250
757-1SS389TL3FD	1SS389(TL3,F,D)	ESC-2	10V	1A	.07	.065	.058	.053
757-1SS405TL3FD	1SS405(TL3,F,D)	ESC-2	20V	1A	.07	.065	.058	.053
757-1SS314TPH3F	1SS314TPH3F	USC-2	30V	100mA	.12	.098	.084	.076
757-1SS416TL4D	1SS416(TL4,D)	FSC-2	30V	1A	.07	.068	.06	.056
757-1SS417CT(TPL3)	1SS417CT(TPL3)	CST-2	40V	0.1A	.14	.11	.094	.086
757-1SS423(TE85L,F)	1SS423(TE85L,F)	SSM-3	40V	0.1A	.28	.22	.19	.17
757-1SS388TL3FD	1SS388(TL3,F,D)	ESC-2	40V	1A	.07	.062	.055	.051
757-1SS387CT(TPL3)	1SS387CT(TPL3)	ESC-2	80V	100mA	.09	.07	.06	.055
757-1SS427(TPL3)	1SS427(TPL3)	UF6-2	80V	100mA	.09	.07	.06	.055
757-1SS184TE85LF	1SS184(TE85L,F)	S-MINI-3	80V	0.1A	.42	.30	.237	.18
757-1SS193SLF	1SS193SLF	SC-59	80V	1A	.05	.045	.04	.037
757-1SS301SU,LF	1SS301SU,LF	SC-70	80V	1A	.05	.045	.04	.037
757-1SS387TL3FD	1SS387(TL3,F,D)	ESC-2	80V	1A	.05	.045	.04	.037
757-1SS181SLF	1SS181SLF	SC-59	80V	2A	.05	.045	.04	.037
757-1SS184SLF	1SS184SLF	SC-59	80V	2A	.05	.045	.04	.037
757-1SS403(TPH3,F)	1SS403(TPH3,F)	USC-2	200V	100mA	.32	.28	.21	.17
757-CRH01(TE85L,Q,M)	CRH01(TE85L,Q,M)	S-FLAT-2	200V	1A	.22	.174	.15	.134
757-CRG05(TE85L,Q)	CRG05(TE85L,Q)	S-FLAT-2	800V	1A	.13	.11	.093	.085

TOSHIBA GENERAL PURPOSE DIODES

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Voltage Output	Average Current	Price Each			
					1	10	100	250
757-CRH01(TE85R,Q,M)	CRH01(TE85R,Q,M)	S-FLAT-2	200V	1A	.22	.174	.15	.134
757-CMF01TE12LQM	CMF01(TE12L,Q,M)	M-FLAT-2	600V	2A	.24	.20	.19	.18

TOSHIBA VARACTOR DIODES

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Voltage (V)	Capacitance (pF)	Price Each			
					1	10	100	250
757-1SV277TPH3F	1SV277TPH3F	USC-2	10V	4.0 to 4.9	.20	.16	.136	.124
757-1SV310TPH3F	1SV310TPH3F	USC-2	10V	9.7 to 11.1	.21	.17	.145	.132
757-1SV270TPH3F	1SV270TPH3F	USC-2	10V	15 to 17	.20	.16	.136	.124
757-1SV304TPH3F	1SV304TPH3F	USC-2	10V	17.3 to 19.3	.21	.17	.145	.132
757-1SV239TPH3F	1SV239TPH3F	USC-2	15V	3.8 to 4.7	.23	.18	.153	.14
757-1SV229TPH3F	1SV229TPH3F	USC-2	15V	14 to 16	.20	.16	.136	.124
757-1SV262TPH3F	1SV262TPH3F	USC-2	34V	33 to 38	.30	.24	.21	.18

TOSHIBA ZENER DIODES

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Reverse Voltage	Power Dissipation	Price Each			
					1	10	100	250
757-CRZ10(TE85L,Q)	CRZ10(TE85L,Q)	S-FLAT-2	10V	0.7W	.38	.30	.26	.23
757-CRZ15(TE85L,Q)	CRZ15(TE85L,Q)	S-FLAT-2	15V	0.7W	.38	.30	.26	.23
757-CRZ30(TE85L,Q)	CRZ30(TE85L,Q)	S-FLAT-2	30V	0.7W	.38	.30	.26	.23

TOSHIBA ESD SUPPRESSORS



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Reverse Voltage	Capacitance (pF)	Power Dissipation	Price Each			
						1	10	100	250
757-DF2B68M1ACTTPL3	DF2B6.8M1ACT(TPL3)	SOD-882	5V	0.5	-	.28	.23	.208	.168
757-DF2S68UCTTPL3	DF2S6.8UCT(TPL3)	CST-2	5V	1.6	150	.11	.09	.078	.063
757-DF2S68SCTPL3	DF2S6.8SCT(TPL3)	SC-2	5V	15	150	.14	.12	.104	.084
757-DF2B68M2SCTPL3	DF2B6.8M2SCT(TPL3)	SC-2	6V	0.4	-	.11	.09	.078	.063
757-DF2B6.8FSTPL4D	DF2B6.8FS(TPL4,D)	FSC-2	7.8V	15	150	.08	.076	.068	.063
757-DF2S6.8FSTL4D	DF2S6.8FS(TL4,D)	FSC-2	7.8V	15	150	.07	.068	.06	.056