

CENTRAL Transistors

Products may be RoHS compliant. Check mouser.com for RoHS status.



Transistors



SMALL SIGNAL TRANSISTORS - LEADED

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Central Part No.	Package	h _{FE}		f _T (MHz) MIN	Price Each			
			Min.	Max		1	25	100	250
NPN Small Signal Transistors									
610-2N1480	2N1480	TO-39	20	60	1.5	2.32	2.25	2.16	2.07
610-2N5785	2N5785	TO-39	20	100	1	3.30	2.92	2.64	2.48
610-2N918	2N918	TO-72	20	-	600	3.87	3.70	3.56	3.40
610-2N2925	2N2925	TO-92	25	235	160	.28	.261	.235	.218
610-2N708	2N708	TO-18	30	120	400	1.42	1.33	1.22	1.14
610-2N3114	2N3114	TO-39	30	120	40	4.43	4.31	4.14	3.97
610-2N5225	2N5225	TO-92	30	600	50	.29	.26	.24	.22
610-2N718A	2N718A	TO-18	40	120	60	1.45	1.16	1.04	.982
610-2N697A	2N697A	TO-39	40	120	50	1.29	1.19	1.12	1.02
610-2N2218A	2N2218A	TO-39	40	120	250	1.29	1.19	1.12	1.02
610-2N3420	2N3420	TO-39	40	120	40	4.40	4.26	4.10	3.93
610-2N3421	2N3421	TO-39	40	120	40	2.64	2.42	2.20	1.98
610-2N4895	2N4895	TO-39	40	120	50	8.13	7.32	6.65	6.10
610-MPSA20	MPSA20	TO-92	40	400	125	.31	.277	.25	.222
610-MPSA42	MPSA42	TO-92	40	-	50	.21	.171	.142	.128
610-2N3708	2N3708	TO-92	45	660	-	.30	.24	.22	.20
610-2N2270	2N2270	TO-39	50	200	100	1.31	1.27	1.22	1.17
610-2N3903	2N3903	TO-92	50	150	250	.36	.338	.316	.283
610-2N4124	2N4124	TO-92	50	200	300	.23	.213	.192	.18
610-2N5770	2N5770	TO-92	50	200	800	.35	.32	.28	.25
610-2N4013	2N4013	TO-18	60	150	300	1.31	1.29	1.27	1.25
610-2N3725A	2N3725A	TO-39	60	150	300	4.32	3.88	3.45	3.02
610-2N2405	2N2405	TO-39	60	200	50	1.04	1.01	.98	.97
610-2N4410	2N4410	TO-92	60	400	60	.28	.261	.235	.218
610-MPSH10	MPSH10	TO-92	60	-	650	.35	.32	.28	.26
610-2N3416	2N3416	TO-92	75	225	-	.78	.64	.52	.413
610-2N5551	2N5551	TO-92	80	250	100	.78	.64	.52	.413
610-2N3107	2N3107	TO-39	100	300	70	2.29	2.18	2.09	1.96
610-2N3501	2N3501	TO-39	100	300	150	5.20	5.09	4.91	4.79
610-2N3704	2N3704	TO-92	100	300	100	.40	.38	.36	.34
610-2N5209	2N5209	TO-92	100	300	30	.43	.38	.34	.30
610-MPS3704	MPS3704	TO-92	100	300	100	.34	.30	.28	.26
610-MPS3706	MPS3706	TO-92	100	300	100	.34	.32	.29	.27
610-PN2222A	PN2222A	TO-92	100	300	300	.18	.16	.14	.12
610-PN3569	PN3569	TO-92	100	300	60	.98	.894	.805	.715
610-PN3643	PN3643	TO-92	100	300	250	.26	.25	.23	.22
610-2N3707	2N3707	TO-92	100	400	-	.81	.77	.73	.66
610-2N5172	2N5172	TO-92	100	500	200	.28	.23	.21	.19
610-2N2924	2N2924	TO-92	150	300	160	.87	.768	.564	.444
610-2N3392	2N3392	TO-92	150	300	120	.30	.28	.25	.23
610-2N3860	2N3860	TO-92	150	300	90	.30	.27	.24	.218
610-MPS3392	MPS3392	TO-92	150	300	-	.26	.24	.22	.20
610-PN3565	PN3565	TO-92	150	600	40	.17	.15	.14	.12
610-2N5961	2N5961	TO-92	170	700	100	.18	.17	.15	.14
610-2N3415	2N3415	TO-92	180	540	-	.78	.64	.52	.413
610-2N3417	2N3417	TO-92	180	540	-	.78	.64	.52	.413
610-2N4424	2N4424	TO-92	180	540	-	.28	.261	.235	.218
610-2N3711	2N3711	TO-92	180	660	-	.30	.28	.25	.23
610-MPS6520	MPS6520	TO-92	200	400	-	.29	.27	.25	.23
610-2N3117	2N3117	TO-18	250	500	60	4.43	4.31	4.14	3.97
610-MPS8097	MPS8097v	TO-92	250	5	-	.30	.25	.20	.16

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Central Part No.	Package	h _{FE}		f _T (MHz) MIN	Price Each			
			Min.	Max		1	25	100	250
NPN Small Signal Transformers (Cont.)									
610-2N3391A	2N3391A	TO-92	250	500	120	.47	.43	.39	.36
610-2N5232A	2N5232A	TO-92	250	500	-	.24	.23	.22	.21
610-MPS6515	MPS6515	TO-92	250	500	-	.27	.22	.17	.14
610-2N5088	2N5088	TO-92	300	900	50	.28	.261	.235	.218
610-2N5962	2N5962	TO-92	600	1400	100	.24	.22	.20	.18
610-2N5306	2N5306	TO-92	7000	70000	60	.52	.448	.356	.29
610-2N5308	2N5308	TO-92	7000	70000	60	.52	.448	.356	.29
610-MPS5306	MPS5306	TO-92	7000	70000	60	.26	.22	.20	.18
610-MPSA28	MPSA28	TO-92	10000	-	125	.30	.27	.25	.22
610-2N6427	2N6427	TO-92	14000	140000	130	.28	.261	.235	.218
610-2N6426	2N6426	TO-92	20000	200000	-	.28	.261	.235	.218
610-MPSA14	MPSA14	TO-92	20000	-	125	.33	.254	.201	.137
610-2N706A	2N706A	TO-18	-	-	-	1.42	1.33	1.22	1.14
PNP Small Signal Transistors									
610-2N4208	2N4208	TO-18	30	120	700	4.68	4.48	4.31	4.15
610-2N4234	2N4234	TO-39	30	150	3	1.65	1.49	1.32	1.22
610-2N5322	2N5322	TO-39	30	150	50	1.64	1.56	1.48	1.42
610-PN3640	PN3640	TO-92	30	120	500	.55	.50	.44	.41
610-2N5226	2N5226	TO-92	30	600	50	.24	.223	.20	.189
610-2N2904A	2N2904A	TO-39	40	120	200	1.26	1.18	1.12	1.03
610-2N4030	2N4030	TO-39	40	120	100	1.29	1.19	1.12	1.02
610-2N3250	2N3250	TO-18	50	150	250	1.42	1.33	1.22	1.14
610-2N3905	2N3905	TO-92	50	150	200	.36	.338	.316	.283
610-PN4356	PN4356	TO-92	50	250	100	.31	.29	.28	.26
610-PN5138	PN5138	TO-92	50	800	30	.25	.23	.21	.19
610-MPSA55	MPSA55	TO-92	50	-	50	.24	.19	.15	.12
610-2N3702	2N3702	TO-92	60	300	100	.25	.222	.20	.182
610-MPS6517	MPS6517	TO-92	90	180	-	.22	.195	.165	.156
610-2N3504	2N3504	TO-18	100	300	200	.87	.82	.79	.74
610-2N3505	2N3505	TO-18	100	300	200	.81	.72	.65	.61
610-2N3962	2N3962	TO-18	100	450	40	1.80	1.68	1.55	1.42
610-2N3502	2N3502	TO-39	100	300	200	.81	.72	.65	.61
610-2N3906	2N3906	TO-92	100	300	250	.25	.23	.22	.21
610-2N4403	2N4403	TO-92	100	300	200	.28	.261	.235	.218
610-2N5366	2N5366	TO-92	100	300	250	.21	.19	.17	.15
610-PN2907A	PN2907A	TO-92	100	300	200	.16	.14	.13	.11
610-PN3644	PN3644	TO-92	100	300	200	.22	.20	.18	.16
610-PN3645	PN3645	TO-92	100	300	200	.34	.31	.27	.24
610-PN4249	PN4249	TO-92	100	300	40	.18	.17	.15	.14
610-PN4355	PN4355	TO-92	100	400	100	.28	.261	.235	.218
610-MPSA06	MPSA06	TO-92	100	-	50	.27	.25	.22	.20
610-2N4126	2N4126	TO-92	120	360	250	.28	.261	.235	.218
610-MPS6519	MPS6519	TO-92	250	500	-	.38	.36	.34	.31
610-PN4250A	PN4250A	TO-92	250	700	50	.31	.25	.18	.13
610-2N5087	2N5087	TO-92	250	800	40	.28	.261	.235	.218
610-MPSA63	MPSA63	TO-92	10000	-	125	.30	.285	.255	.234
610-MPSA77	MPSA77	TO-92	10000	-	125	.35	.322	.288	.264
610-MPSA64	MPSA64	TO-92	20000	-	125	.30	.285	.255	.234