

PANASONIC SEMICONDUCTOR Transistors **Panasonic**

RoHS Compliant This product is RoHS compliant.

COMPOSITE TRANSISTORS WITH BUILT-IN RESISTORS (CONT.)

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Panasonic Part No.	Package	Polarity	VCEO (Max) (V)	IC (Max) (mA)	Input Resistor (R1) (kΩ)	Base-Emitter Resistor (R2) (kΩ)	Price Each		
								1	25	100
NPN x 2 (Cont.)										
667-DMC961030R	DMC961030R	SSMini5-F4-B	NPN x 2	50	100	47	47	.31	.308	.30
667-DMC961040R	DMC961040R	SSMini5-F4-B	NPN x 2	50	100	10	47	.31	.308	.30
667-DMC964010R	DMC964010R	SSMini6-F3-B	NPN x 2	50	100	10	10	.31	.308	.30
667-DMC964020R	DMC964020R	SSMini6-F3-B	NPN x 2	50	100	22	22	.31	.308	.30
667-DMC964040R	DMC964040R	SSMini6-F3-B	NPN x 2	50	100	10	47	.31	.308	.30
667-DMC964050R	DMC964050R	SSMini6-F3-B	NPN x 2	50	100	10	-	.31	.308	.30
667-DMC964060R	DMC964060R	SSMini6-F3-B	NPN x 2	50	100	4.7	-	.31	.308	.30
667-DMC964070R	DMC964070R	SSMini6-F3-B	NPN x 2	50	100	22	-	.31	.308	.30
667-DMC9640N0R	DMC9640N0R	SSMini6-F3-B	NPN x 2	50	100	4.7	47	.31	.308	.30
667-DMC961010R	DMC961010R	SSMini5-F4-B	NPN x 2	50	100	10	10	.31	.308	.30
667-DMC961020R	DMC961020R	SSMini5-F4-B	NPN x 2	50	100	22	22	.31	.308	.30
667-DMC961030R	DMC961030R	SSMini5-F4-B	NPN x 2	50	100	47	47	.31	.308	.30
667-DMC961040R	DMC961040R	SSMini5-F4-B	NPN x 2	50	100	10	47	.31	.308	.30
667-DMC964010R	DMC964010R	SSMini6-F3-B	NPN x 2	50	100	10	10	.31	.308	.30
667-DMC964020R	DMC964020R	SSMini6-F3-B	NPN x 2	50	100	22	22	.31	.308	.30
667-DMC964040R	DMC964040R	SSMini6-F3-B	NPN x 2	50	100	10	47	.31	.308	.30
667-DMC964050R	DMC964050R	SSMini6-F3-B	NPN x 2	50	100	10	-	.31	.308	.30
667-DMC964060R	DMC964060R	SSMini6-F3-B	NPN x 2	50	100	4.7	-	.31	.308	.30
667-DMC964070R	DMC964070R	SSMini6-F3-B	NPN x 2	50	100	22	-	.31	.308	.30
667-DMC9640N0R	DMC9640N0R	SSMini6-F3-B	NPN x 2	50	100	4.7	47	.31	.308	.30
667-DMC561010R	DMC561010R	SMMini5-F3-B	NPN x 2	50	100	10	10	.17	.166	.162
667-DMC561050R	DMC561050R	SMMini5-F3-B	NPN x 2	50	100	10	-	.17	.166	.162
667-DMC561060R	DMC561060R	SMMini5-F3-B	NPN x 2	50	100	4.7	-	.17	.166	.162
667-DMC5610E0R	DMC5610E0R	SMMini5-F3-B	NPN x 2	50	100	47	22	.17	.166	.162
667-DMC562050R	DMC562050R	SMMini5-F3-B	NPN x 2	50	100	10	-	.17	.166	.162
667-DMC564000R	DMC564000R	SMMini6-F3-B	NPN x 2	50	100	47	-	.17	.166	.162
667-DMC564030R	DMC564030R	SMMini6-F3-B	NPN x 2	50	100	47	47	.17	.166	.162
667-DMC566000R	DMC566000R	SMMini6-F3-B	NPN x 2	50	100	47	-	.17	.166	.162
667-DMC566030R	DMC566030R	SMMini6-F3-B	NPN x 2	50	100	47	47	.17	.166	.162
667-DMC5610M0R	DMC5610M0R	SMMini5-F3-B	NPN x 2	50	100	2.2	47	.13	.128	.125
667-DMC5640L0R	DMC5640L0R	SMMini6-F3-B	NPN x 2	50	100	4.7	4.7	.12	.113	.11
667-DMC9610M0R	DMC9610M0R	SSMini5-F4-B	NPN x 2	50	100	2.2	47	.31	.308	.30
667-DMC964030R	DMC964030R	SSMini6-F3-B	NPN x 2	50	100	47	47	.31	.308	.30
667-DMC264020R	DMC264020R	Mini6-G4-B	NPN x 2	50	100	22	22	.15	.145	.141
PNP x 2										
667-DMA564040R	DMA564040R	SMMini6-F3-B	PNP x 2	-50	-100	10	47	.17	.166	.162
667-DMA564050R	DMA564050R	SMMini6-F3-B	PNP x 2	-50	-100	10	-	.17	.166	.162
667-DMA566010R	DMA566010R	SMMini6-F3-B	PNP x 2	-50	-100	10	-	.17	.166	.162
667-DMA566020R	DMA566020R	SMMini6-F3-B	PNP x 2	-50	-100	22	22	.17	.166	.162
667-DMA566030R	DMA566030R	SMMini6-F3-B	PNP x 2	-50	-100	47	47	.17	.166	.162
667-DMA566040R	DMA566040R	SMMini6-F3-B	PNP x 2	-50	-100	10	47	.17	.166	.162
667-DMA566050R	DMA566050R	SMMini6-F3-B	PNP x 2	-50	-100	10	-	.17	.166	.162
667-DMA566060R	DMA566060R	SMMini6-F3-B	PNP x 2	-50	-100	4.7	-	.17	.166	.162
667-DMA261000R	DMA261000R	Mini5-G3-B	PNP x 2	-50	-100	47	-	.15	.145	.141
667-DMA261010R	DMA261010R	Mini5-G3-B	PNP x 2	-50	-100	10	10	.15	.145	.141
667-DMA261020R	DMA261020R	Mini5-G3-B	PNP x 2	-50	-100	22	22	.15	.145	.141
667-DMA261030R	DMA261030R	Mini5-G3-B	PNP x 2	-50	-100	47	47	.15	.145	.141
667-DMA261040R	DMA261040R	Mini5-G3-B	PNP x 2	-50	-100	10	47	.15	.145	.141
667-DMA261050R	DMA261050R	Mini5-G3-B	PNP x 2	-50	-100	10	-	.15	.145	.141
667-DMA261060R	DMA261060R	Mini5-G3-B	PNP x 2	-50	-100	4.7	-	.15	.145	.141
667-DMA261090R	DMA261090R	Mini5-G3-B	PNP x 2	-50	-100	1	10	.15	.145	.141
667-DMA2610F0R	DMA2610F0R	Mini5-G3-B	PNP x 2	-50	-100	4.7	10	.15	.145	.141
667-DMA2610H0R	DMA2610H0R	Mini5-G3-B	PNP x 2	-50	-100	2.2	10	.15	.145	.141
667-DMA2610M0R	DMA2610M0R	Mini5-G3-B	PNP x 2	-50	-100	2.2	47	.15	.145	.141
667-DMA264010R	DMA264010R	Mini6-G4-B	PNP x 2	-50	-100	10	10	.15	.145	.141
667-DMA264020R	DMA264020R	Mini6-G4-B	PNP x 2	-50	-100	22	22	.15	.145	.141
667-DMA264030R	DMA264030R	Mini6-G4-B	PNP x 2	-50	-100	47	47	.15	.145	.141
667-DMA264040R	DMA264040R	Mini6-G4-B	PNP x 2	-50	-100	10	47	.15	.145	.141
667-DMA264050R	DMA264050R	Mini6-G4-B	PNP x 2	-50	-100	10	-	.15	.145	.141
667-DMA264060R	DMA264060R	Mini6-G4-B	PNP x 2	-50	-100	4.7	-	.15	.145	.141
667-DMA266030R	DMA266030R	Mini6-G4-B	PNP x 2	-50	-100	47	47	.15	.142	.138
667-DMA561080R	DMA561080R	SMMini5-F3-B	PNP x 2	-50	-100	0.51	5.1	.12	.118	.115
667-DMA564030R	DMA564030R	SMMini6-F3-B	PNP x 2	-50	-100	47	47	.17	.166	.162
667-DMA564020R	DMA564020R	SMMini6-F3-B	PNP x 2	-50	-100	22	22	.17	.166	.162
667-DMA564010R	DMA564010R	SMMini6-F3-B	PNP x 2	-50	-100	10	10	.17	.166	.162
667-DMA561030R	DMA561030R	SMMini5-F3-B	PNP x 2	-50	-100	47	47	.17	.166	.162
667-DMA561010R	DMA561010R	SMMini5-F3-B	PNP x 2	-50	-100	10	10	.17	.166	.162
667-DMA561000R	DMA561000R	SMMini5-F3-B	PNP x 2	-50	-100	47	-	.17	.166	.162
667-DMA961030R	DMA961030R	SSMini5-F4-B	PNP x 2	-50	-100	47	47	.31	.308	.30
667-DMA9610F0R	DMA9610F0R	SSMini5-F4-B	PNP x 2	-50	-100	4.7	10	.31	.308	.30
667-DMA964010R	DMA964010R	SSMini6-F3-B	PNP x 2	-50	-100	10	10	.31	.308	.30
667-DMA964020R	DMA964020R	SSMini6-F3-B	PNP x 2	-50	-100	22	22	.31	.308	.30
667-DMA964060R	DMA964060R	SSMini6-F3-B	PNP x 2	-50	-100	4.7	-	.31	.308	.30
667-DMA964070R	DMA964070R	SSMini6-F3-B	PNP x 2	-50	-100	22	-	.31	.308	.30
667-DMA9640M0R	DMA9640M0R	SSMini6-F3-B	PNP x 2	-50	-100	2.2	47	.31	.308	.30
667-DMA961040R	DMA961040R	SSMini5-F4-B	PNP x 2	-50	-100	10/47	10/47	.13	.127	.124
667-DMA561070R	DMA561070R	SMMini5-F3-B	PNP x 2	-50	-100	22	-	.17	.166	.162
667-DMA564060R	DMA564060R	SMMini6-F3-B	PNP x 2	-50	-100	4.7	-	.17	.166	.162
667-DMA564070R	DMA564070R	SMMini6-F3-B	PNP x 2	-50	-100	22	-	.17	.166	.162
667-DMA5640M0R	DMA5640M0R	SMMini6-F3-B	PNP x 2	-50	-100	22	47	.17	.166	.162
667-DMA961010R	DMA961010R	SSMini5-F4-B	PNP x 2	-50	-100	10	10	.31	.308	.30
667-DMA964030R	DMA964030R	SSMini6-F3-B	PNP x 2	-50	-100	47	47	.31	.308	.30
667-DMA9640T0R	DMA9640T0R	SSMini6-F3-B	PNP x 2	-50	-100	22	47	.31	.308	.30
PNP/NPN										
667-DMG563010R	DMG563010R	SMMini5-F3-B	PNP/NPN	-50/50	-100/100	10	10	.17	.166	.162
667-DMG563020R	DMG563020R	SMMini5-F3-B	PNP/NPN	-50/50	-100/100	22	22	.17	.166	.162
667-DMG563H10R	DMG563H10R	SMMini5-F3-B	PNP/NPN	-50/50	-100/100	47/4.7	47/10	.17	.166	.162
667-DMG563H50R	DMG563H50R	SMMini5-F3-B	PNP/NPN	-50/50	-100/100	47/10	47/47	.17	.166	.162
667-DMG564030R	DMG564030R	SMMini6-F3-B	PNP/NPN	-50/50	-100/100	47	47	.17	.166	.162
667-DMG564040R	DMG564040R	SMMini6-F3-B	PNP/NPN	-50/50	-100/100	10	47	.17	.166	.162
667-DMG564050R	DMG564050R	SMMini6-F3-B	PNP/NPN	-50/50	-100/100	10	-	.17	.166	.162
667-DMG564060R	DMG564060R	SMMini6-F3-B	PNP/NPN	-50/50	-100/100	47	-	.17	.166	.162
667-DMG5640N0R	DMG5640N0R	SMMini6-F3-B	PNP/NPN	-50/50	-100/100	4.7	47	.17	.166	.162
667-DMG564H20R	DMG564H20R	SMMini6-F3-B	PNP/NPN	-50/50	-100/100	4.7/1	47/10	.17	.166	.162
667-DMG963030R	DMG963030R	SSMini5-F4-B	PNP/NPN	-50/50	-100/100	47	47	.15	.121	.118