

# PANASONIC SEMICONDUCTOR Transistors



RoHS Compliant This product is RoHS compliant.

## TRANSISTORS WITH BUILT-IN RESISTORS (CONT.)

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Panasonic Part No.	Package	Polarity	VCEO (Max) (V)	IC (Max) (mA)	Input Resistor (R1) (kΩ)	Base-Emitter Resistor (R2) (kΩ)	Price Each		
								1	25	100
NPN (Cont.)										
667-DRC9114TOL	DRC9114TOL	SSMini3-F3-B	NPN	50	100	10	-	.15	.083	.081
667-DRC9114WOL	DRC9114WOL	SSMini3-F3-B	NPN	50	100	10	4.7	.15	.083	.081
667-DRC9114YOL	DRC9114YOL	SSMini3-F3-B	NPN	50	100	10	47	.15	.083	.081
667-DRC9115EOL	DRC9115EOL	SSMini3-F3-B	NPN	50	100	100	-	.15	.083	.081
667-DRC9115GOL	DRC9115GOL	SSMini3-F3-B	NPN	50	100	-	100	.15	.083	.081
667-DRC9115TOL	DRC9115TOL	SSMini3-F3-B	NPN	50	100	100	-	.15	.083	.081
667-DRC9123EOL	DRC9123EOL	SSMini3-F3-B	NPN	50	100	2.2	2.2	.15	.083	.081
667-DRC9123JOL	DRC9123JOL	SSMini3-F3-B	NPN	50	100	2.2	47	.15	.083	.081
667-DRC9124EOL	DRC9124EOL	SSMini3-F3-B	NPN	50	100	22	22	.15	.083	.081
667-DRC9124TOL	DRC9124TOL	SSMini3-F3-B	NPN	50	100	22	-	.15	.083	.081
667-DRC9124XOL	DRC9124XOL	SSMini3-F3-B	NPN	50	100	22	47	.15	.083	.081
667-DRC9143EOL	DRC9143EOL	SSMini3-F3-B	NPN	50	100	4.7	4.7	.15	.083	.081
667-DRC9143TOL	DRC9143TOL	SSMini3-F3-B	NPN	50	100	4.7	-	.15	.083	.081
667-DRC9143XOL	DRC9143XOL	SSMini3-F3-B	NPN	50	100	4.7	10	.15	.083	.081
667-DRC9143YOL	DRC9143YOL	SSMini3-F3-B	NPN	50	100	4.7	22	.15	.083	.081
667-DRC9143ZOL	DRC9143ZOL	SSMini3-F3-B	NPN	50	100	4.7	47	.15	.083	.081
667-DRC9144EOL	DRC9144EOL	SSMini3-F3-B	NPN	50	100	47	47	.15	.083	.081
667-DRC9144GOL	DRC9144GOL	SSMini3-F3-B	NPN	50	100	-	47	.15	.083	.081
667-DRC9144TOL	DRC9144TOL	SSMini3-F3-B	NPN	50	100	47	-	.15	.083	.081
667-DRC9144VOL	DRC9144VOL	SSMini3-F3-B	NPN	50	100	47	10	.15	.083	.081
667-DRC9144WOL	DRC9144WOL	SSMini3-F3-B	NPN	50	100	47	22	.15	.083	.081
667-DRC9152ZOL	DRC9152ZOL	SSMini3-F3-B	NPN	50	100	0.51	5.1	.15	.083	.081
667-DRC5113ZOL	DRC5113ZOL	SMini3-F2-B	NPN	50	100	1	10	.08	.079	.077
667-DRC5114EOL	DRC5114EOL	SMini3-F2-B	NPN	50	100	10	10	.08	.079	.077
667-DRC5114TOL	DRC5114TOL	SMini3-F2-B	NPN	50	100	10	-	.08	.079	.077
667-DRC5114WOL	DRC5114WOL	SMini3-F2-B	NPN	50	100	10	4.7	.08	.079	.077
667-DRC5114YOL	DRC5114YOL	SMini3-F2-B	NPN	50	100	10	47	.08	.079	.077
667-DRC5115EOL	DRC5115EOL	SMini3-F2-B	NPN	50	100	100	100	.08	.079	.077
667-DRC5115TOL	DRC5115TOL	SMini3-F2-B	NPN	50	100	100	-	.08	.079	.077
667-DRC5123EOL	DRC5123EOL	SMini3-F2-B	NPN	50	100	2.2	2.2	.08	.079	.077
667-DRC5123JOL	DRC5123JOL	SMini3-F2-B	NPN	50	100	2.2	47	.08	.079	.077
667-DRC5124EOL	DRC5124EOL	SMini3-F2-B	NPN	50	100	22	22	.08	.079	.077
667-DRC5124TOL	DRC5124TOL	SMini3-F2-B	NPN	50	100	22	-	.08	.079	.077
667-DRC5124XOL	DRC5124XOL	SMini3-F2-B	NPN	50	100	22	47	.08	.079	.077
667-DRC5143EOL	DRC5143EOL	SMini3-F2-B	NPN	50	100	4.7	4.7	.08	.079	.077
667-DRC5143TOL	DRC5143TOL	SMini3-F2-B	NPN	50	100	4.7	-	.08	.079	.077
667-DRC5143XOL	DRC5143XOL	SMini3-F2-B	NPN	50	100	4.7	10	.08	.079	.077
667-DRC5143YOL	DRC5143YOL	SMini3-F2-B	NPN	50	100	4.7	22	.08	.079	.077
667-DRC5143ZOL	DRC5143ZOL	SMini3-F2-B	NPN	50	100	4.7	47	.08	.079	.077
667-DRC5144EOL	DRC5144EOL	SMini3-F2-B	NPN	50	100	47	47	.08	.079	.077
667-DRC5144GOL	DRC5144GOL	SMini3-F2-B	NPN	50	100	-	47	.08	.079	.077
667-DRC5144TOL	DRC5144TOL	SMini3-F2-B	NPN	50	100	47	-	.08	.079	.077
667-DRC5144VOL	DRC5144VOL	SMini3-F2-B	NPN	50	100	47	10	.08	.079	.077
667-DRC5144WOL	DRC5144WOL	SMini3-F2-B	NPN	50	100	47	22	.08	.079	.077
667-DRC5152ZOL	DRC5152ZOL	SMini3-F2-B	NPN	50	100	0.51	5.1	.08	.079	.077
667-DRC2115EOL	DRC2115EOL	Mini3-G3-B	NPN	50	100	100	100	.08	.078	.076
667-DRC2115GOL	DRC2115GOL	Mini3-G3-B	NPN	50	100	-	100	.08	.078	.076
667-DRC2113ZOL	DRC2113ZOL	Mini3-G3-B	NPN	50	100	1	10	.10	.075	.073
667-DRC2114EOL	DRC2114EOL	Mini3-G3-B	NPN	50	100	10	10	.10	.075	.073
667-DRC2114TOL	DRC2114TOL	Mini3-G3-B	NPN	50	100	10	-	.10	.075	.073
667-DRC2114WOL	DRC2114WOL	Mini3-G3-B	NPN	50	100	10	4.7	.10	.075	.073
667-DRC2114YOL	DRC2114YOL	Mini3-G3-B	NPN	50	100	10	47	.10	.075	.073
667-DRC2123EOL	DRC2123EOL	Mini3-G3-B	NPN	50	100	2.2	2.2	.10	.075	.073
667-DRC2123JOL	DRC2123JOL	Mini3-G3-B	NPN	50	100	2.2	47	.10	.075	.073
667-DRC2124EOL	DRC2124EOL	Mini3-G3-B	NPN	50	100	22	22	.10	.075	.073
667-DRC2124TOL	DRC2124TOL	Mini3-G3-B	NPN	50	100	22	-	.10	.075	.073
667-DRC2124XOL	DRC2124XOL	Mini3-G3-B	NPN	50	100	22	47	.10	.074	.073
667-DRC2143EOL	DRC2143EOL	Mini3-G3-B	NPN	50	100	4.7	4.7	.10	.075	.073
667-DRC2143TOL	DRC2143TOL	Mini3-G3-B	NPN	50	100	4.7	-	.10	.075	.073
667-DRC2143XOL	DRC2143XOL	Mini3-G3-B	NPN	50	100	4.7	10	.10	.075	.073
667-DRC2143YOL	DRC2143YOL	Mini3-G3-B	NPN	50	100	4.7	22	.10	.075	.073
667-DRC2143ZOL	DRC2143ZOL	Mini3-G3-B	NPN	50	100	4.7	47	.10	.075	.073
667-DRC2144EOL	DRC2144EOL	Mini3-G3-B	NPN	50	100	47	47	.10	.075	.073
667-DRC2144GOL	DRC2144GOL	Mini3-G3-B	NPN	50	100	-	47	.10	.075	.073
667-DRC2144TOL	DRC2144TOL	Mini3-G3-B	NPN	50	100	47	-	.10	.075	.073
667-DRC2144VOL	DRC2144VOL	Mini3-G3-B	NPN	50	100	47	10	.10	.075	.073
667-DRC2144WOL	DRC2144WOL	Mini3-G3-B	NPN	50	100	47	22	.10	.075	.073
667-DRC2152ZOL	DRC2152ZOL	Mini3-G3-B	NPN	50	100	0.51	5.1	.10	.075	.073
667-DRC2115TOL	DRC2115TOL	Mini3-G3-B	NPN	50	100	100	-	.07	.068	.067
PNP										
667-DRA3143XOL	DRA3143XOL	SSSMini3-F2-B	PNP	-50	-100	4.7	10	.14	.104	.101
667-DRA3144EOL	DRA3144EOL	SSSMini3-F2-B	PNP	-50	-100	47	47	.14	.104	.101
667-DRA3114EOL	DRA3114EOL	SSSMini3-F2-B	PNP	-50	-100	10	10	.15	.104	.101
667-DRA3114TOL	DRA3114TOL	SSSMini3-F2-B	PNP	-50	-100	10	-	.15	.104	.101
667-DRA3114YOL	DRA3114YOL	SSSMini3-F2-B	PNP	-50	-100	10	47	.15	.104	.101
667-DRA3115EOL	DRA3115EOL	SSSMini3-F2-B	PNP	-50	-100	100	100	.15	.104	.101
667-DRA3115GOL	DRA3115GOL	SSSMini3-F2-B	PNP	-50	-100	-	100	.15	.104	.101
667-DRA3115TOL	DRA3115TOL	SSSMini3-F2-B	PNP	-50	-100	100	-	.15	.104	.101
667-DRA3123EOL	DRA3123EOL	SSSMini3-F2-B	PNP	-50	-100	2.2	2.2	.15	.104	.101
667-DRA3123JOL	DRA3123JOL	SSSMini3-F2-B	PNP	-50	-100	2.2	2.2	.15	.104	.101
667-DRA3124EOL	DRA3124EOL	SSSMini3-F2-B	PNP	-50	-100	22	22	.15	.104	.101
667-DRA3124TOL	DRA3124TOL	SSSMini3-F2-B	PNP	-50	-100	22	-	.15	.104	.101
667-DRA3124XOL	DRA3124XOL	SSSMini3-F2-B	PNP	-50	-100	22	47	.15	.104	.101
667-DRA3143TOL	DRA3143TOL	SSSMini3-F2-B	PNP	-50	-100	4.7	-	.15	.104	.101
667-DRA3143YOL	DRA3143YOL	SSSMini3-F2-B	PNP	-50	-100	4.7	22	.15	.104	.101
667-DRA3143ZOL	DRA3143ZOL	SSSMini3-F2-B	PNP	-50	-100	4.7	47	.15	.104	.101
667-DRA3144TOL	DRA3144TOL	SSSMini3-F2-B	PNP	-50	-100	47	-	.15	.104	.101
667-DRA3144VOL	DRA3144VOL	SSSMini3-F2-B	PNP	-50	-100	47	22	.15	.104	.101
667-DRA3152ZOL	DRA3152ZOL	SSSMini3-F2-B	PNP	-50	-100	0.51	5.1	.15	.104	.101
667-DRA3113ZOL	DRA3113ZOL	SSSMini3-F2-B	PNP	-50	-100	1	10	.10	.095	.092
667-DRA3123YOL	DRA3123YOL	SSSMini3-F2-B	PNP	-50	-100	2.2	10	.09	.086	.084
667-DRA3143EOL	DRA3143EOL	SSSMini3-F2-B	PNP	-50	-100	4.7	4.7	.09	.086	.084
667-DRA3144VOL	DRA3144VOL	SSSMini3-F2-B	PNP	-50	-100	47	10	.09	.086	.084

Transistors

Panasonic Semiconductor

NEW SUPPLIER

NEW SUPPLIER

NEW SUPPLIER