

PANASONIC SEMICONDUCTOR Transistors



This product is RoHS compliant.

TRANSISTORS WITH BUILT-IN RESISTORS (CONT.)

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Panasonic Part No.	Package	Polarity	VCEO (Max) (V)	IC (Max) (mA)	Input Resistor (R1) (kΩ)	Base-Emitter Resistor (R2) (kΩ)	Price Each		
								1	25	100
PNP (Cont.)										
667-DRA2514E0L	DRA2514E0L	Mini3-G3-B	PNP	-50	-500	10	10	.24	.236	.229
667-DRA2522J0L	DRA2522J0L	Mini3-G3-B	PNP	-50	-500	0.27	5	.24	.236	.229
667-DRA2523E0L	DRA2523E0L	Mini3-G3-B	PNP	-50	-500	2.2	2.2	.24	.236	.229
667-DRA2523Y0L	DRA2523Y0L	Mini3-G3-B	PNP	-50	-500	2.2	10	.24	.236	.229
667-DRA2543E0L	DRA2543E0L	Mini3-G3-B	PNP	-50	-500	4.7	4.7	.24	.236	.229
667-DRA5114T0L	DRA5114T0L	SMini3-F2-B	PNP	-50	-100	10	-	.11	.079	.077
667-DRA2533Q0L	DRA2533Q0L	Mini3-G3-B	PNP	-50	-500	3.1	4.6	.15	.106	.104
667-DRA9113Z0L	DRA9113Z0L	SSMini3-F3-B	PNP	-50	-100	1	10	.10	.083	.081
667-DRA9114E0L	DRA9114E0L	SSMini3-F3-B	PNP	-50	-100	10	10	.10	.083	.081
667-DRA9114T0L	DRA9114T0L	SSMini3-F3-B	PNP	-50	-100	10	-	.10	.083	.081
667-DRA9114Y0L	DRA9114Y0L	SSMini3-F3-B	PNP	-50	-100	10	47	.10	.083	.081
667-DRA9115E0L	DRA9115E0L	SSMini3-F3-B	PNP	-50	-100	100	100	.10	.083	.081
667-DRA9115G0L	DRA9115G0L	SSMini3-F3-B	PNP	-50	-100	-	100	.10	.083	.081
667-DRA9115T0L	DRA9115T0L	SSMini3-F3-B	PNP	-50	-100	100	-	.10	.083	.081
667-DRA9123E0L	DRA9123E0L	SSMini3-F3-B	PNP	-50	-100	2.2	2.2	.10	.083	.081
667-DRA9123J0L	DRA9123J0L	SSMini3-F3-B	PNP	-50	-100	2.2	47	.10	.083	.081
667-DRA9123Y0L	DRA9123Y0L	SSMini3-F3-B	PNP	-50	-100	2.2	10	.10	.083	.081
667-DRA9124E0L	DRA9124E0L	SSMini3-F3-B	PNP	-50	-100	22	22	.10	.083	.081
667-DRA9124T0L	DRA9124T0L	SSMini3-F3-B	PNP	-50	-100	22	-	.10	.083	.081
667-DRA9124X0L	DRA9124X0L	SSMini3-F3-B	PNP	-50	-100	22	47	.10	.083	.081
667-DRA9143E0L	DRA9143E0L	SSMini3-F3-B	PNP	-50	-100	4.7	4.7	.10	.083	.081
667-DRA9143T0L	DRA9143T0L	SSMini3-F3-B	PNP	-50	-100	4.7	-	.10	.083	.081
667-DRA9143X0L	DRA9143X0L	SSMini3-F3-B	PNP	-50	-100	4.7	10	.10	.083	.081
667-DRA9143Y0L	DRA9143Y0L	SSMini3-F3-B	PNP	-50	-100	4.7	22	.10	.083	.081
667-DRA9143Z0L	DRA9143Z0L	SSMini3-F3-B	PNP	-50	-100	4.7	47	.10	.083	.081
667-DRA9144E0L	DRA9144E0L	SSMini3-F3-B	PNP	-50	-100	47	47	.10	.083	.081
667-DRA9144T0L	DRA9144T0L	SSMini3-F3-B	PNP	-50	-100	47	-	.10	.083	.081
667-DRA9144V0L	DRA9144V0L	SSMini3-F3-B	PNP	-50	-100	47	10	.10	.083	.081
667-DRA9144W0L	DRA9144W0L	SSMini3-F3-B	PNP	-50	-100	47	22	.10	.083	.081
667-DRA9152Z0L	DRA9152Z0L	SSMini3-F3-B	PNP	-50	-100	0.51	5.1	.10	.083	.081
667-DRA5113Z0L	DRA5113Z0L	SMini3-F2-B	PNP	-50	-100	1	10	.08	.079	.077
667-DRA5114E0L	DRA5114E0L	SMini3-F2-B	PNP	-50	-10	10	10	.08	.079	.077
667-DRA5114Y0L	DRA5114Y0L	SMini3-F2-B	PNP	-50	-100	10	47	.08	.079	.077
667-DRA5115E0L	DRA5115E0L	SMini3-F2-B	PNP	-50	-100	100	100	.08	.079	.077
667-DRA5115G0L	DRA5115G0L	SMini3-F2-B	PNP	-50	-100	100	-	.08	.079	.077
667-DRA5115T0L	DRA5115T0L	SMini3-F2-B	PNP	-50	-100	100	-	.08	.079	.077
667-DRA5123E0L	DRA5123E0L	SMini3-F2-B	PNP	-50	-100	2.2	2.2	.08	.079	.077
667-DRA5123J0L	DRA5123J0L	SMini3-F2-B	PNP	-50	-100	2.2	47	.08	.079	.077
667-DRA5123Y0L	DRA5123Y0L	SMini3-F2-B	PNP	-50	-100	2.2	10	.08	.079	.077
667-DRA5124E0L	DRA5124E0L	SMini3-F2-B	PNP	-50	-100	22	22	.08	.079	.077
667-DRA5124T0L	DRA5124T0L	SMini3-F2-B	PNP	-50	-100	22	-	.08	.079	.077
667-DRA5124X0L	DRA5124X0L	SMini3-F2-B	PNP	-50	-100	22	47	.08	.079	.077
667-DRA5143E0L	DRA5143E0L	SMini3-F2-B	PNP	-50	-100	4.7	4.7	.08	.079	.077
667-DRA5143T0L	DRA5143T0L	SMini3-F2-B	PNP	-50	-100	4.7	-	.08	.079	.077
667-DRA5143X0L	DRA5143X0L	SMini3-F2-B	PNP	-50	-100	4.7	10	.08	.079	.077
667-DRA5143Y0L	DRA5143Y0L	SMini3-F2-B	PNP	-50	-100	4.7	22	.08	.079	.077
667-DRA5143Z0L	DRA5143Z0L	SMini3-F2-B	PNP	-50	-100	4.7	47	.08	.079	.077
667-DRA5144E0L	DRA5144E0L	SMini3-F2-B	PNP	-50	-100	47	47	.08	.079	.077
667-DRA5144T0L	DRA5144T0L	SMini3-F2-B	PNP	-50	-100	47	-	.08	.079	.077
667-DRA5144V0L	DRA5144V0L	SMini3-F2-B	PNP	-50	-100	47	10	.08	.079	.077
667-DRA5144W0L	DRA5144W0L	SMini3-F2-B	PNP	-50	-100	47	22	.08	.079	.077
667-DRA5152Z0L	DRA5152Z0L	SMini3-F2-B	PNP	-50	-100	0.51	5.1	.08	.079	.077
667-DRA5L14Y0L	DRA5L14Y0L	SMini3-F2-B	PNP	-30	-100	10	47	.08	.079	.077
667-DRA2115E0L	DRA2115E0L	Mini3-G3-B	PNP	-50	-100	100	100	.08	.079	.077
667-DRA2115G0L	DRA2115G0L	Mini3-G3-B	PNP	-50	-100	-	100	.08	.079	.077
667-DRA2115T0L	DRA2115T0L	Mini3-G3-B	PNP	-50	-100	100	-	.08	.079	.077
667-DRA2124X0L	DRA2124X0L	Mini3-G3-B	PNP	-50	-100	22	47	.09	.075	.073
667-DRA2113Z0L	DRA2113Z0L	Mini3-G3-B	PNP	-50	-100	1	10	.09	.075	.073
667-DRA2114E0L	DRA2114E0L	Mini3-G3-B	PNP	-50	-100	10	10	.09	.075	.073
667-DRA2114T0L	DRA2114T0L	Mini3-G3-B	PNP	-50	-100	10	-	.09	.075	.073
667-DRA2114Y0L	DRA2114Y0L	Mini3-G3-B	PNP	-50	-100	10	47	.09	.075	.073
667-DRA2123E0L	DRA2123E0L	Mini3-G3-B	PNP	-50	-100	2.2	2.2	.09	.075	.073
667-DRA2123J0L	DRA2123J0L	Mini3-G3-B	PNP	-50	-100	2.2	47	.09	.075	.073
667-DRA2123Y0L	DRA2123Y0L	Mini3-G3-B	PNP	-50	-100	2.2	10	.09	.075	.073
667-DRA2124E0L	DRA2124E0L	Mini3-G3-B	PNP	-50	-100	22	22	.09	.075	.073
667-DRA2124T0L	DRA2124T0L	Mini3-G3-B	PNP	-50	-100	22	-	.09	.075	.073
667-DRA2143E0L	DRA2143E0L	Mini3-G3-B	PNP	-50	-100	4.7	4.7	.09	.075	.073
667-DRA2143T0L	DRA2143T0L	Mini3-G3-B	PNP	-50	-100	4.7	-	.09	.075	.073
667-DRA2143X0L	DRA2143X0L	Mini3-G3-B	PNP	-50	-100	4.7	10	.09	.075	.073
667-DRA2143Y0L	DRA2143Y0L	Mini3-G3-B	PNP	-50	-100	4.7	22	.09	.075	.073
667-DRA2143Z0L	DRA2143Z0L	Mini3-G3-B	PNP	-50	-100	4.7	47	.09	.075	.073
667-DRA2144E0L	DRA2144E0L	Mini3-G3-B	PNP	-50	-100	47	47	.09	.075	.073
667-DRA2144T0L	DRA2144T0L	Mini3-G3-B	PNP	-50	-100	47	-	.09	.075	.073
667-DRA2144V0L	DRA2144V0L	Mini3-G3-B	PNP	-50	-100	47	10	.09	.075	.073
667-DRA2144W0L	DRA2144W0L	Mini3-G3-B	PNP	-50	-100	47	22	.09	.075	.073
667-DRA2152Z0L	DRA2152Z0L	Mini3-G3-B	PNP	-50	-100	0.51	5.1	.09	.075	.073
667-DRA2L14Y0L	DRA2L14Y0L	Mini3-G3-B	PNP	-30	-100	10	47	.08	.07	.069