

LITTELFUSE Fuses



This page of product is compliant.



3AB CERAMIC FUSES (CONT.)



MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Volts (V)	Price Each			
					1	10	100	250
322 Series Very Fast-Acting Fuses								
576-0322020.HXP	0322020.HXP	A	20	65	4.90	4.50	3.90	3.34
576-0322030.HXP	0322030.HXP	A	30	65	5.00	4.89	4.79	4.25
324 Series Fast-Acting Fuses								
576-0324010.HXP	0324010.HXP	A	10	250	1.21	1.14	1.09	1.03
576-0324012.HXP	0324012.HXP	A	12	250	1.21	1.14	1.09	1.03
576-0324015.HXP	0324015.HXP	A	15	250	1.21	1.14	1.09	1.03
576-0324020.HXP	0324020.HXP	A	20	250	1.58	1.48	1.42	1.35
576-0324025.HXP	0324025.HXP	A	25	250	1.58	1.48	1.42	1.35
576-0324030.HXP	0324030.HXP	A	30	250	1.58	1.48	1.42	1.35
325 Series Slo-Blo® Fuses								
576-0325010.HXP	0325010.HXP	A	10	250	1.73	1.64	1.55	1.47
576-0325015.HXP	0325015.HXP	A	15	250	1.73	1.64	1.55	1.47
576-0325020.HXP	0325020.HXP	A	30	250	1.73	1.64	1.55	1.47
576-0325030.HXP	0325030.HXP	A	20	250	1.73	1.64	1.55	1.47
326 Series Slo-Blo® Ceramic Fuses								
576-0326.010HXP	0326.010HXP	A	0.01	250	2.95	2.80	2.64	2.51
576-0326.031HXP	0326.031HXP	A	0.031	250	2.95	2.80	2.64	2.51
576-0326.100HXP	0326.100HXP	A	0.1	250	2.95	2.80	2.64	2.51
576-0326.250HXP	0326.250HXP	A	0.25	250	1.47	1.37	1.13	1.02
576-0326.375HXP	0326.375HXP	A	0.375	250	1.47	1.37	1.13	1.02
576-0326.500HXP	0326.500HXP	A	0.5	250	1.47	1.37	1.13	1.02
576-0326.750HXP	0326.750HXP	A	0.75	250	1.47	1.37	1.13	1.02
576-0326.800HXP	0326.800HXP	A	0.8	250	1.47	1.37	1.13	1.02
576-0326001.HXP	0326001.HXP	A	1	250	1.47	1.37	1.13	1.02
576-032601.5HXP	032601.5HXP	A	1.5	250	1.47	1.37	1.13	1.02
576-0326002.HXP	0326002.HXP	A	2	250	1.47	1.37	1.13	1.02
576-032602.5HXP	032602.5HXP	A	2.5	250	1.47	1.37	1.13	1.02
576-0326003.HXP	0326003.HXP	A	3	250	1.47	1.37	1.13	1.02
576-0326004.HXP	0326004.HXP	A	4	250	1.47	1.37	1.13	1.02
576-0326005.HXP	0326005.HXP	A	5	250	1.47	1.37	1.13	1.02
576-03266.25HXP	03266.25HXP	A	6.25	250	1.47	1.37	1.13	1.02
576-0326007.HXP	0326007.HXP	A	7	250	1.47	1.37	1.13	1.02
576-0326008.HXP	0326008.HXP	A	8	250	1.47	1.37	1.13	1.02
576-0326010.HXP	0326010.HXP	A	10	250	1.47	1.37	1.13	1.02
576-0326012.HXP	0326012.HXP	A	12	250	1.47	1.37	1.13	1.02
576-0326015.HXP	0326015.HXP	A	15	250	1.47	1.37	1.13	1.02
576-0326020.HXP	0326020.HXP	A	20	250	1.47	1.37	1.13	1.02
576-0326025.HXP	0326025.HXP	A	25	250	1.47	1.37	1.13	1.02
576-0326030.HXP	0326030.HXP	A	30	250	1.47	1.37	1.13	1.02
506 Series Fast-Acting Fuses								
576-0506015.MXP	0506015.MXP	A	15	600	5.50	4.85	4.00	3.56
576-0506016.MXP	0506016.MXP	A	16	600	5.50	4.85	4.00	3.56
576-0506020.MXP	0506020.MXP	A	20	600	5.50	4.85	4.00	3.56

Features (508 Series):

- Superior Interrupting rating of 10,000 Amperes
- Compact form with or without axial leads

Applications:

- Used as supplementary protection in appliance or utilization equipment to provide individual protection for components or internal circuits



MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Volts (V)	Price Each			
					1	10	100	250
508 Series High Voltage Fuses								
576-0508.315MXP	0508.315MXP	A	0.315	1	8.92	7.70	6.48	5.76
576-0508.500MXP	0508.500MXP	A	0.5	1	8.92	7.70	6.48	5.76
576-0508001.MXP	0508001.MXP	A	1	1	8.92	7.70	6.48	5.76
576-0508001.MXP	0508001.MXP	A	1	1	7.86	7.03	5.58	4.96

SPF SOLAR FUSES 1000 VOLT

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Price Each			
				1	10	100	250
576-0SPF001.T	0SPF001.T	B	1	30.88	24.57	19.65	18.95
576-0SPF003.T	0SPF003.T	B	3	30.88	24.57	19.65	18.95
576-0SPF005.T	0SPF005.T	B	5	30.88	24.57	19.65	18.95
576-0SPF006.T	0SPF006.T	B	6	30.88	24.57	19.65	18.95
576-0SPF008.T	0SPF008.T	B	8	29.41	23.39	18.71	18.04
576-0SPF010.T	0SPF010.T	B	10	30.88	24.57	19.65	18.95
576-0SPF015.T	0SPF015.T	B	15	38.05	36.35	34.65	34.11
576-0SPF020.T	0SPF020.T	B	20	30.88	24.57	19.65	18.95
576-0SPF025.T	0SPF025.T	B	25	30.88	24.57	19.65	18.95
576-0SPF030.T	0SPF030.T	B	30	30.88	24.57	19.65	18.95

LPHV Series - Fuseholder

576-LPHV0001Z	LPHV0001Z	C	30	22.99	18.28	14.63	14.10
576-LPHV0003Z	LPHV0003Z	C	30	74.17	70.86	62.72	59.88
576-LPHV0004Z	LPHV0004Z	C	30	94.07	91.12	83.62	79.43

SPFR SERIES SOLAR FUSES

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Price Each			
				1	10	100	250
576-SPFR250.X	SPFR250.X	D	250	493.60	469.71	425.66	367.47
576-SPFR300.X	SPFR300.X	D	300	470.09	447.34	416.00	379.74
576-SPFR350.X	SPFR350.X	D	350	470.09	447.34	416.00	379.74
576-SPFR400.X	SPFR400.X	D	400	493.60	469.71	425.66	367.47
SPFR Series - Solar Fuseholder							
576-SPFRHD4001ST	SPFRHD4001ST	-	400	359.83	297.79	239.88	230.29

SPFJ SERIES 1000 VOLT

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Price Each			
				1	10	100	250
576-SPFJ125.X	SPFJ125.X	D	125	257.79	214.83	171.86	165.72
576-SPFJ160.X	SPFJ160.X	D	160	257.79	214.83	171.86	165.72
576-SPFJ200.X	SPFJ200.X	D	200	257.79	214.83	171.86	165.72
576-SPFJ250.X	SPFJ250.X	D	250	517.35	431.13	344.90	332.58
576-SPFJ300.X	SPFJ300.X	D	300	517.35	431.13	344.90	332.58
576-SPFJ350.X	SPFJ350.X	D	350	517.35	431.13	344.90	332.58
576-SPFJ400.X	SPFJ400.X	D	400	517.35	431.13	344.90	332.58
576-SPFJ450.X	SPFJ450.X	D	450	815.10	674.56	543.40	521.66
SPFJ Series - Solar Fuseholder							
576-LFJ102001C	LFJ102001C	E	200	219.45	209.00	198.55	188.10
576-LFJ104001C	LFJ104001C	E	400	400.15	381.10	362.05	342.98
576-LFJ104501C	LFJ104501C	E	450	654.22	623.08	591.94	560.76

CLK SERIES MIDGET AC FAST ACTING FUSES 600 VOLTS



For quantities greater than listed, call for quote.

576-0KLK001.T	0KLK001.T	--	1	26.00	24.00	19.60	18.00
576-0KLK002.T	0KLK002.T	--	2	26.00	24.00	19.60	18.00
576-0KLK005.T	0KLK005.T	--	5	26.00	24.00	19.60	18.00
576-0KLK010.T	0KLK010.T	--	10	26.00	24.00	19.60	18.00
576-0KLK015.T	0KLK015.T	--	15	26.00	24.00	19.60	18.00
576-0KLK020.T	0KLK020.T	--	20	26.00	23.79	20.00	18.50
576-0KLK025.T	0KLK025.T	--	25	26.00	23.79	20.00	18.50
576-0KLK030.T	0KLK030.T	--	30	26.00	23.79	20.00	18.50

FLQ SERIES MIDGET AC SLO-BLO FUSES 500 VOLTS



For quantities greater than listed, call for quote.

576-0FLQ001.T	0FLQ001.T	--	1	23.68	20.72	16.57	15.98
576-0FLQ015.T	0FLQ015.T	--	15	23.68	20.72	16.57	15.98
576-0FLQ020.T	0FLQ020.T	--	20	23.68	20.72	16.57	15.98
576-0FLQ025.T	0FLQ025.T	--	25	23.68	20.72	16.57	15.98

KLKD SERIES MIDGET AC/DC FAST ACTING FUSES 600 VOLTS



For quantities greater than listed, call for quote.

576-KLKD.300T	KLKD.300T	--	0.3	28.66	27.94	22.78	21.52
576-KLKD001.T	KLKD001.T	--	1	24.04	21.03	16.82	16.22
576-KLKD005.T	KLKD005.T	--	5	24.04	21.03	16.82	16.22
576-KLKD008.T	KLKD008.T	--	8	25.32	22.15	17.24	17.09
576-KLKD010.T	KLKD010.T	--	10	24.04	21.03	16.82	16.22
576-KLKD015.T	KLKD015.T	--	15	24.04	21.03	16.82	16.22
576-KLKD020.T	KLKD020.T	--	20	25.98	22.73	18.18	17.53

KLDR CLASS CC TIME-DELAY FUSES FOR TRANSFORMERS 600/300V (AC/DC)



For quantities greater than listed, call for quote.

576-KLDR.100T	KLDR.100T	--	0.1	31.41	29.87	28.32	27.50
576-KLDR.200T	KLDR.200T	--	0.2	30.71	30.06	25.23	23.94
576-KLDR.300T	KLDR.300T	--	0.3	35.71	34.95	29.33	27.84
576-KLDR.500T	KLDR.500T	--					