

LEDIL OY Secondary Optics



This product is RoHS compliant.



LED Lighting

LEDil OY

NEW SUPPLIER

NEW SUPPLIER

NEW SUPPLIER

OPTICS FOR AVAGO JADE SERIES LEDS

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ledil OY Part No.	Dia. (mm)	Angle (FWHM)	Optic Type	Price Each	
					1	50
928-CA12346T12RSW	CA12346_TINA2-RS	16.1	15	Single Lens	2.13	1.51
928-CA12347T12DWD	CA12347_TINA2-D	16.1	17	Single Lens	2.13	1.51
928-CA12348T12MWW	CA12348_TINA2-M	16.1	30	Single Lens	2.13	1.51
928-CA12349T12OW	CA12349_TINA2-O	16.1	36+18	Single Lens	2.13	1.51
928-CA12350T12WW	CA12350_TINA2-W	16.1	51	Single Lens	2.13	1.51

OPTICS FOR LEDENGIN LEDS

MOUSER STOCK NO.	Ledil OY Part No.	Dia. (mm)	Angle (FWHM)	Optic Type	Price Each	
					1	50
928-FA10784LE1RS	FCN10784_LE1-RS	21.6	8	Single Lens	2.19	1.57
928-FA10786LE1D	FCN10786_LE1-D	21.6	10	Single Lens	2.19	1.57
928-FA10783LE1M	FCN10783_LE1-M	21.6	24	Single Lens	2.19	1.57
928-FCN11454LE1M2	FCN11454_LE1-M2	21.6	30	Single Lens	2.19	1.57
928-FA10785LE1REC	FCN10785_LE1-REC	21.6	38+24	Single Lens	2.19	1.57
928-FA11103LE1O90	FCN11103_LE1-O-90	21.6	40+20	Single Lens	2.19	1.57

LZ1/LZ4 Series

928-C10437BR	C10437_BOOMERANG	19.8	28/32	Reflector	2.91	2.09
--------------	------------------	------	-------	-----------	------	------

OPTICS FOR LUMINUS DEVICES LEDS

SST-50/SST-90 Series

MOUSER STOCK NO.	Ledil OY Part No.	Dia. (mm)	Angle (FWHM)	Optic Type	Price Each
928-C10977LILYS	C10977_LILY-S	22.6	20/24	Reflector	2.46 1.76
928-C10978LILYM	C10978_LILY-M	22.6	30/26	Reflector	2.46 1.76
928-C10979LILYW	C10979_LILY-W	22.6	45/56	Reflector	2.46 1.76

OPTICS FOR CREE

MP-L Series

MOUSER STOCK NO.	Ledil OY Part No.	Dia. (mm)	Angle (FWHM)	Optic Type	Price Each
928-C11394TS	C11394_TYRA-S	40	20	Reflector	2.56 2.19
928-C11395TM	C11395_TYRA-M	40	32	Reflector	2.56 2.19
928-C11396TW	C11396_TYRA-W	40	52	Reflector	2.06 1.76
928-CA11475T2ST	CA11475_TYRA2-S	40	20	Reflector	2.59 2.22
928-CA11476T2MT	CA11476_TYRA2-M	40	32	Reflector	2.59 2.22
928-CA11477T2WT	CA11477_TYRA2-W	40	52	Reflector	2.59 2.22

MT-G Series

928-C12095MNM	C12095_MINNIE-M	32.4	26	Reflector	2.29 1.63
928-C12097MNVVV	C12097_MINNIE-WVV	32.4	74	Reflector	2.29 1.63

MT-G/MT-G2 Series

928-CA12239MNM	CA12239_MINNIE-M	35	26/27	Reflector	2.65 1.89
928-CA12240MNVVV	CA12240_MINNIE-WVV	35	74/69	Reflector	2.65 1.89

MX-3, MX-6 Series

MOUSER STOCK NO.	Ledil OY Part No.	Dia. (mm)	Angle (FWHM)	Optic Type	Price Each
928-C12226SFW	C12226_STRADA-FW	Rect	Asym	Single Lens	2.13 1.51
928-CA12238SFW	CA12238_STRADA-FW	Rect	Asym	Single Lens	2.55 1.81

MX-6 Series LEDs

MOUSER STOCK NO.	Ledil OY Part No.	Dia. (mm)	Angle (FWHM)	Optic Type	Price Each
928-CA11171TRSBLK	CA11171_TINA2-RS	16.1	18	Single Lens	2.46 1.75
928-CA11172TINA2DBLK	CA11172_TINA2-D	16.1	20	Single Lens	2.46 1.75
928-CA11174TINA2MBLK	CA11174_TINA2-M	16.1	30	Single Lens	2.46 1.75
928-CA11175T2WBK	CA11175_TINA2-W	16.1	40	Single Lens	2.46 1.75
928-CA11176TINA2WBK	CA11176_TINA2-WW	16.1	56	Single Lens	2.46 1.75
928-CA11173TINA2OBLK	CA11173_TINA2-O	16.1	34+21	Single Lens	2.46 1.75
928-FA10696LN2RS	FA10696_LN2-RS	21.6	14	Single Lens	2.67 1.90
928-FA10695LN2D	FA10695_LN2-D	21.6	18	Single Lens	2.67 1.90
928-FA10697LN2M	FA10697_LN2-M	21.6	26	Single Lens	2.67 1.90
928-FA11452LN2M2	FA11452_LN2-M2	21.6	30	Single Lens	2.67 1.90

OPTICS FOR VARIOUS LED SUPPLIERS

MOUSER STOCK NO.	Ledil OY Part No.	Dia. (mm)	Optic Type	CREE Series (Angle FWHM)						OSRAM OS (Angle FWHM)				Price Each	
				XP-E	XP-G	XB-D	XM-L	XM-L HV	XT-E	SSL-80	SSL-150	Square EC	Square PC	1	50
928-FA11905T3S	FA11905_TINA3-S	16.1	Single Lens	10	15	-	23	-	-	11	9	-	-	2.67	1.90
928-FA11904T3WWW	FA11904_TINA3-WWW	16.1	Single Lens	-	-	-	70	80	54	46	-	-	-	2.67	1.90
928-CA11663HEIDIRS	CA11663_HEIDI-RS	21.6	Single Lens	8	9	8	-	-	-	6	7	12	-	2.67	1.90
928-CA11264HEIDID	CA11264_HEIDI-D	21.6	Single Lens	10	12	12	-	-	10	7	9	10	-	2.67	1.90
928-CA11265HEIDIM	CA11265_HEIDI-M	21.6	Single Lens	28	28	29	-	-	-	28	26	29	-	2.67	1.90
928-CA11268HEIDIW	CA11268_HEIDI-W	21.6	Single Lens	32	31	30	-	-	-	32	32	34	-	2.67	1.90
928-CA11266HEIDIO	CA11266_HEIDI-O	21.6	Single Lens	48+10	47+14	54+10	-	-	-	47+8	50+8	48+12	-	2.67	1.90
928-CA11267HEIDIO90	CA11267_HEIDI-O-90	21.6	Single Lens	9+50	14+44	12+49	-	-	-	9+42	9+48	12+48	-	2.67	1.90
928-CA11387EMILYSS	CA11387_EMILY-SS	26	Single Lens	10	11	-	-	-	-	11	12	-	-	2.67	1.90
928-CA11388EMILYM	CA11388_EMILY-M	26	Single Lens	18	18	-	-	-	-	18	20	-	-	2.67	1.90
928-CA11389EMILYO	CA11389_EMILY-O	26	Single Lens	44+9	44+10	-	-	-	-	44+10	44+12	-	-	2.67	1.90
928-CA11390EMILYO90	CA11390_EMILY-O-90	26	Single Lens	49+9	44+10	-	-	-	-	44+10	44+12	-	-	2.67	1.90
928-C12086SFW	C12086_STRADA-FW	15.4x19.6	Single Lens	Asym	Asym	-	Asym	Asym	Asym	Asym	Asym	-	-	2.46	1.76
928-C12087STFW	CA12087_STRADA-FW	15.4x19.6	Single Lens	Asym	Asym	-	Asym	Asym	Asym	Asym	Asym	-	-	2.54	1.81
928-C11425STRADATDW	C11425_STRADA-T-DW	19.6x15.5	Single Lens	Asym	Asym	-	-	-	-	Asym	Asym	-	-	2.46	1.76
928-C11249STRADAS	C11249_STRADA-S	19.6x15.5	Single Lens	144+168	144+176	-	-	-	-	161	146+170	-	-	2.46	1.76
928-C11252STRADAC2	C11252_STRADA-C2	19.6x15.5	Single Lens	124	136	135	-	-	-	92	92	-	-	2.46	1.76
928-CA11253STRADAC2N	CA11253_STRADA-C2	19.6x15.5	Single Lens	124	132	135	-	-	-	92	92	-	-	2.94	2.10
928-C11415STRADATDN	C11415_STRADA-T-DN	19.8x15.5	Single Lens	Asym	Asym	-	-	-	-	Asym	Asym	-	-	2.46	1.76
928-C11192TUIJA3SS	C11192_TUIJA-3-SS	50	3in 1 Lens	12	14	11	-	-	-	10	12	-	-	4.26	3.05
928-C11193TUIJA3M	C11193_TUIJA-3-M	50	3in 1 Lens	19	20	16	-	-	-	14	23	-	-	4.26	3.05
928-C11191TUIJA3W	C11191_TUIJA-3-W	50	3in 1 Lens	58	59	49	-	-	-	46	58	-	-	4.26	3.05
928-C11710ANNA403S	C11710_ANNA-40-3-S	40	3in 1 Lens	12	18	-	-	-	-	11	12	-	-	3.99	2.85
928-C11711ANNA403M	C11711_ANNA-40-3-M	40	3in 1 Lens	19	25	22	-	-	-	20	22	-	-	3.99	2.85
928-C11712ANNA403W	C11712_ANNA-40-3-W	40	3in 1 Lens	36	36	29	-	-	-	26	34	-	-	3.99	2.85
928-C11793ANNA404S	C11793_ANNA-40-4-S	40	4in 1 Lens	12	18	-	-	-	-	11	12	-	-	3.99	2.85
928-C11794ANNA404M	C11794_ANNA-40-4-M	40	4in 1 Lens	19	25	22	-	-	-	20	22	-	-	3.99	2.85
928-C11795ANNA404W	C11795_ANNA-40-4-W	40	4in 1 Lens	36	36	29	-	-	-	26	34	-	-	3.99	2.85
928-C11713A405S	C11713_ANNA-40-5-S	40	5in 1 Lens	12	18	-	-	-	-	11	12	-	-	3.99	2.85
928-C11714ANNA405M	C11714_ANNA-40-5-M	40	5in 1 Lens	19	25	22	-	-	-	20	22	-	-	3.99	2.85
928-C11715ANNA405W	C11715_ANNA-40-5-W	40	5in 1 Lens	36	36	29	-	-	-	26	34	-	-	3.99	2.85
928-C11805ANNA406S	C11805_ANNA-40-6-S	40	6in 1 Lens	19	18	-	-	-	-	11	12	-	-	3.99	2.85
928-C11806ANNA406M	C11806_ANNA-40-6-M	40	6in 1 Lens	19	25	22	-	-	-	20	22	-	-	3.99	2.85
928-C11807ANNA406W	C11807_ANNA-40-6-W	40	6in 1 Lens	36	36	29	-	-	-	26	34	-	-	3.99	2.85
928-C11918ST6X1DNW	C11918_STRADA-T-6X1-DNW	119.8x25.2	6in 1 Lens	Asym	Asym	Asym	-	-	-	Asym	Asym	-	Asym	8.13	5.82
928-C11716ANNA407S	C11716_ANNA-40-7-S	40	7in 1 Lens	12	18	-	-	-	-	11	12	-	-	3.99	2.85
928-C11717ANNA407M	C11717_ANNA-40-7-M	40	7in 1 Lens	19	25	22	-	-	-	20	22	-	-	3.99	2.85
928-C11718ANNA407W	C11718_ANNA-40-7-W	40	7in 1 Lens	36	36	29	-	-	-	26	34	-	-	3.99	2.85

