



Pushing Performance

Han shielded module basic, male



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 027 3021
Specification	Han shielded module basic, male
HARTING eCatalogue	https://b2b.harting.com/09140273021

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Shielded module basic
Description of the module	With 180° shielding element

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	27
Additional contacts	+ shielding
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.09 ... 0.52 mm²
Rated current	4 A
Rated voltage	32 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Commercial data

Packaging size	1
Net weight	0.01 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440218 Module for industrial connectors (data)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09140273021