

## Han shielded module basic, female



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 027 3121
Specification	Han shielded module basic, female
HARTING eCatalogue	<a href="https://b2b.harting.com/09140273121">https://b2b.harting.com/09140273121</a>

### Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Shielded module basic
Description of the module	With 180° shielding element

### Version

Termination method	Crimp termination
Gender	Female
Number of contacts	27
Additional contacts	+ shielding
Details	Please order crimp contacts separately.

### Technical characteristics

Conductor cross-section	0.09 ... 0.52 mm <sup>2</sup>
Rated current	4 A
Rated voltage	32 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

## Commercial data

Packaging size	1
Net weight	0.01 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440218 Module for industrial connectors (data)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09140273121](#)