




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORPORATION.



PANDUIT PART NO.	BUNDLE DIA MIN - MAX.	DIMENSIONS			MATERIAL	COLOR	WEIGHT g/100 pcs
		'A'	'B'	'C'			
HCME06Y12-...30	8.0 - 12.0	15.8	10.0	19.2	HEAT STABILIZED NYLON 6/6	BLACK	208



SCALE: FULL

NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, AND COLOR.
2. (*) DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINK MARKS.
3. APPLICATION SPECIFICATION:
PUNCHED RECTANGULAR HOLE: 3.5 x 8.0 mm
PANEL THICKNESS: 0.8 - 4.0 mm



APPLICATION
SPECIFICATION
DETAIL VIEW

CAD FILENAME/LAYERS		G01932BR_PB_HCME06Y12_03		
PANDUIT		CORP.		
		TINLEY PARK, ILLINOIS		
HARNESS CLIP FOR EDGE MOUNT				
Unless otherwise specified, all dimensions are metric tolerance; $\pm 0.5\text{mm}$				
DRAWN BY	JAD	MAT'L:	SCALE	
DATE	5-4-01	SEE ABOVE	NONE	
CHK'D			DRAWING NO.	DWG
			GB1932BR	A
				SIZE

3	5/14/04	JAD		ADD WEIGHT	GB1932BR	3			
2	4/29/03	JAD		NEW RELEASE, WAS GERMAN FK000FA REV 3	GB1932BR	2			
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[HCME06Y12-M30](#)