


AVERY DENNISON MARKETING SPECIFICATION

THE SUBJECT MATTER DISCLOSED HEREIN EMBODIES PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF THE AVERY DENNISON CO. NONE OF WHICH SHALL BE COPIED, REPRODUCED, DISCLOSED TO OTHERS, PUBLISHED OR USED IN WHOLE OR IN PART, FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS BEING MADE AVAILABLE WITHOUT THE EXPRESS ADVANCE WRITTEN PERMISSION OF A DULY AUTHORIZED AGENT OF THE COMPANY. THIS DOCUMENT IS THE PROPERTY OF THE AVERY DENNISON CO. AND IS TO BE RETURNED TO THE COMPANY ON DEMAND.

HISTORY

REV.	DATE	DESCRIPTION
B	08.03.18	UPDATES TO NEW FORMAT; ADDED -0 TO PART NUMBER; ADDED SPECIAL CHARACTERISTIC NOTE; RE-NUMBERED DIMS TO CURRENT AVERY DENNISON STD.; BALLOON 8 WAS 54 CHG 54.0



NOTES:

1. Δ = INDICATES SPECIAL CHARACTERISTIC

9	FLAMMABILITY:	HB RATED PER FMVSS302
10	TENSILE STRENGTH:	177.9N / 40 lbf MIN.
	OPERATING TEMP RANGE:	-40°F (-40°C) TO 220°F (105°C)
	WEIGHT:	0.6g
	BUNDLE DIAMETER:	ϕ 17.0mm [.67in] MIN
	TOOL:	12001 - HAND TOOL 12500 - PNEUMATIC TOOL
	TOOL TENSION SETTING:	3-5
	PACKAGING:	1000/BAG, 5 BAGS/MASTER

APPROVALS:	ENG. APPR. <i>Daniel Gilbertson</i> 08.03.18
	Q.A. APPR. <i>Rick Estano</i> 08.03.18
SPECIFIED TOLERANCES ARE:	
$.XX \pm .03$ INCHES	$.X \pm .7$ mm
$.XXX \pm .010$ INCHES	$.XX \pm .25$ mm
ANGULAR: $\pm 2^\circ$	

DESCRIPTION	PART NO.	REV.
CT, 5.5in STOPPER, HS, GREY	20097-0	B



FASTENER DIVISION
FITCHBURG, MA 01420 U.S.A.
TEL: 1-800-225-5913
FAX: 978-333-8157

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[20097-0](#)