





LASER PART/BATCH MARK HERE

USB A FEEDTHROUGH CONNECTOR GROUNDED TO OUTER SHELL



OPTION Y (OPTION Z AT REVERSE END)



OPTION Z (OPTION Y AT REVERSE END)

NOTES

MIL-DTL-38999 STYLE
MATES WITH AMPHENOL USBFTV

MATERIALS

USB A INSERT
CONTACTS 30µ Au/Ni
SHIELDING - NICKEL PLATED BRASS
BODY - PA, UL94V-0
PCB - FR4, UL94V-0

SEAL - SILICONE ELASTOMER
INSULATOR - PPS GL40 UL94-V0, COLOUR BLACK

PERFORMANCE

CURRENT RATING 1 AMP MAX PER CONTACT
VOLTAGE RATING 30V AC
TEMPERATURE -40°C TO +105°C

PC4B0064-15NX-1-C

SERIES
SHELL SIZE
KEY ARRANGEMENT (N, A, B, C, D, E)
INSERT ROTATION (X, Y, Z)
MATERIAL (SEE TABLE)
PLATING (SEE TABLE)
PART NUMBER FOR UNGROUNDED OPTION PC4B0064-15NX-1-C-U

CODE	MATERIAL / PLATING
1-C	ALUMINIUM / ELECTROLESS NICKEL
1-B	ALUMINIUM / CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZB	ALUMINIUM / ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
4-J	STAINLESS STEEL / PASSIVATE
2-Z	NICKEL ALUMINIUM BRONZE / SHOT BLAST

LIST NOT EXHAUSTIVE, FOR COMPREHENSIVE LIST AND SPECS, SEE WEBSITE

DRAWN	R.S.	DATE	01/09/2016
SALES APPR	M.F.	DATE	01/09/2016
DESIGN APPR			
PROD APPR			
QUAL APPR			
ISSUE	REV.	DCR	
1			
NCAGE CODE U5792	WEIGHT		



3RD ANGLE
PROJECTION
NOT TO
SCALE

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS IN MILLIMETRES

GENERAL TOL
LINEAR +/-0,25MM
ANGULAR +/- 1°

MATERIAL

SEE PART NUMBER
BREAKDOWN

FINISH

SEE PART NUMBER
BREAKDOWN

PART NUMBER:

PC4B0064-15**-**-*

TITLE:


USB A BULKHEAD FEEDTHROUGH ASSEMBLY

ASSY USED ON: USB A D38999/20

THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD
IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE
DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.

POLAMCO LTD, WESTON LOCK,
LOWER BRISTOL ROAD
BATH BA2 1EP

SHT
1



Polamco



DRAWING NO:
C4461

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[PC4B0064-15NZ-1-C](#)