

ZMT Series Mini Size Sealed Snap-acting Switches

NEW



Features/Benefits

- IP67 rating / Dust tight protection
- From 0.1A to 5A max. (ultra-low current available)
- Excellent sealed solution for modules mechanisms in Automotive and Medical applications
- UL / ENEC

Typical Applications

- Automotive: door latch, seat position detection, EV charging
- Handheld devices (medical)
- Industrial equipment
- Consumer electronics

Specifications

CONTACT RATING: 0.1A 125/250VAC 3A 24VDC

3A 125/250VAC 3A 24VDC

5A 125/250 VAC 3A 24VDC

ELECTRICAL LIFE: 10,000 cycles

ELECTRICAL OPERATING FREQUENCY: 10-30 operations per minute

MECHANICAL LIFE: 1,000,000 operations

MECHANICAL OPERATING FREQUENCY: 120 operations per minute

INSULATION RESISTANCE: Min. 100 MΩ (500 VDC/minute) between Live-parts and dead metal parts

DIELECTRIC STRENGTH:

500VAC (50-60HZ)/minute between contacts

1500VAC (50-60HZ)/minute between Live-parts and dead metal parts

OPERATING TEMPERATURE: -40°C to 85°C (with no icing)

OPERATING FORCE: 200 grams

Materials

CASE: PBT

COVER: PBT

BUTTON: PBT

MOVABLE CONTACTS: AG alloy

TERMINALS: AG alloy

LEVER: Stainless steel

WIRE: PVC+CU

LOWE CASE: Nylon

RUBBER SEAL: Silicon

Build-A-Switch

Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and place it in the appropriate box.



Electrical Rating

- 01A** 0.1A 125/250VAC (Contact silver plated)
- 03A** 3A 125/250VAC (Contact silver plated)
- 05A** 5A 125/250VAC (Contact silver plated)
- G03** 3A 125/250VAC (Contact gold plated)

Operating Force

- CF** Refer to force table (P00 = 100 gf)
- CJ** Refer to force table (P00 = 170 gf)

Actuator Type

- P00** Pin plunger
- L03** Leaf lever 3.2 mm
- F01** Leaf lever (fold) 1.1 mm
- S02** Simulated leaf roller 1.9 mm
- S05** Simulated leaf roller 5.0 mm
- S06** Simulated leaf roller 5.8 mm
- A01** Roller 0.2 mm
- H03** Hinged lever 3.2 mm
- R05** Hinged simulated leaf roller 5.0 mm

Terminations

- P** PC thru-hole
- S** Solder
- L** Left-footed, PC thru-hole
- R** Right-footed, PC thru-hole
- J** Wire leads out bottom
- K** Wire leads out right side
- W** Wire leads out left side

Circuitry

- C** SPDT
- W** SPST N.C.
- Y** SPST N.O.

Wire Type for J, K, W Terminations

- NONE** AVSS 0.3 mm² (No UL, No ENEC)
- 20** UL1007 20 AWG
- 22** UL1007 22 AWG
- 24** UL1007 24 AWG

Cover & Case Type

- E** E type




NEW

ZMT Series Mini Size Sealed Snap-acting Switches

SERIES

ZMT MINI SIZE SEALED SNAP-ACTING SWITCHES - SP MOMENTARY



ELECTRICAL RATING

Silver Contacts

ZMT	UL1054/UL1058
01A	0.1A 125/250VAC 3A 24VDC
03A	3A 125/250VAC 3A 24VDC
05A	5A 125/250VAC 3A 24VDC

Gold Contacts

ZMT	UL1054/UL1058
G03	3A 125/250VAC 3A 24VDC

- Note: See Technical Data in section N of this catalog for RoHS compliant and compatible definition and specifications.
- All models  with all options.
- Consult Customer Service center for availability and delivery of nonstandard ratings.

OPERATING FORCE

OPERATING CODE	OPERATING FORCE AT THE BOTTOM (OZ / GRAMS)
CF	3.52 / 100
CJ	5.99 / 170

C&K

27 Jan 22

J-11



Dimensions are shown: mm
Specifications and dimensions subject to change

www.ckswitches.com




Snap-acting

ZMT Series Mini Size Sealed Snap-acting Switches


NEW

ACTUATORS


P00 PIN PLUNGER




S02 SIMULATED ROLLER 1.9 MM




F01 LEAF LEVER (FOLD) 1.1 MM




L03 LEAF LEVER 3.2 MM




S06 SIMULATED LEAF ROLLER 5.8 MM




R05 HINGED SIMULATED LEAF ROLLER 5.0 MM




S05 SIMULATED LEAF ROLLER 5.0 MM




H03 HINGED LEVER 3.2 MM



A01 ROLLER 0.2 MM



CODE	OPER. FORCE MAX.(gf)		REL. FORCE MIN.(gf)		A FP MAX. (mm)	B OP MAX. (mm)	C PT MAX. (mm)	D OT MIN. (mm)	E MIN. (mm)
P00	100	170	21	35	6.4	5.9±0.2	0.5	0.2	—
L03	32	56	5	8	9.0	7.1±0.8	3.4	0.6	3.2
S05	28	48	5	7	13.1	9.1±0.8	3.5	0.7	5
F01	58	83	7	11	9.05	8.1±0.6	1.64	0.49	1.1
A01	45	55	4	8	15.45	13.0±1.1	3.5	0.1	0.2
S02	40	50	5	8	11.7	10.1±1.0	3.0	0.6	1.9
S06	45	65	5	12	9.85	8.5±0.8	1.8	0.25	0.1
H03	32	56	5	8	9.0	7.1±0.8	3.4	0.6	3.2
R05	28	48	5	7	13.1	9.1±0.8	3.5	0.7	5



Dimensions are shown: Inch (mm)

Specifications and dimensions subject to change


www.ckswitches.com

NEW


ZMT Series Mini Size Sealed Snap-acting Switches

TERMINATIONS


P PC THRU-HOLE




S SOLDER




L LEFT-FOOTED, PC THRU-HOLE



R RIGHT-FOOTED, PC THRU-HOLE




J WIRE LEADS OUT BOTTOM




COM: UL1007 20AWG/22AWG/24AWG OR EQUIVALENT(BLACK)
 NO: UL1007 20AWG/22AWG/24AWG OR EQUIVALENT(BLUE)
 NC: UL1007 20AWG/22AWG/24AWG OR EQUIVALENT(GRAY)

K WIRE LEADS OUT RIGHT SIDE



COM: UL1007 20AWG/22AWG/24AWG OR EQUIVALENT(BLACK)
 NO: UL1007 20AWG/22AWG/24AWG OR EQUIVALENT(BLUE)
 NC: UL1007 20AWG/22AWG/24AWG OR EQUIVALENT(GRAY)

W WIRE LEADS OUT LEFT SIDE



COM: UL1007 20AWG/22AWG/24AWG OR EQUIVALENT(BLACK)
 NO: UL1007 20AWG/22AWG/24AWG OR EQUIVALENT(BLUE)
 NC: UL1007 20AWG/22AWG/24AWG OR EQUIVALENT(GRAY)

C&K

27 Jan 22

**Snap-acting**

ZMT Series

Mini Size Sealed Snap-acting Switches

NEW

CIRCUITRY

C




SPDT

Y

SPST NO

W

SPST NC



Snap-acting

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Switches:

[ZMT01ACFP00PCE](#) [ZMT03ACJL03RCE](#) [ZMT03ACJP00SCE](#) [ZMT03ACJS02JCE22](#) [ZMT03ACJS05KCE22](#)
[ZMT03ACJS05LCE](#) [ZMT05ACJP00SCE](#) [ZMT05ACJS06JCE20](#) [ZMTG03CJP00PCE](#) [ZMTG03CJS02WCE24](#)