

### High Flow Fume Extractor, 3 Filter Stages, Low Noise (<55dB), 2 Suction Hoses

#### Description

High Flow Fume Extractor, 3 Filter Stages, Low Noise (<55dB), 2 suction hoses. Can be used with just 1 or 2 of the included suction hoses. Comes with suction port cover to block unused suction port when used with only 1 suction hose.

#### Specifications

Voltage: 100-120 VAC  
Frequency: 60Hz  
Rated Output Power: 0.32 KW  
Fuse: T3.15A  
Air Flow: 350 Cubic Meters Per Hour (206 CFM (Cubic Feet Per Minute))  
Noise Level: <55dB  
Case Dimensions (LxWxH): 31 x 31 x 46 cm (12-1/4" x 12-1/4" x 18-1/8")  
Weight: 20 kg (44 lbs)

#### Parts Included

CQ-FE-2  
Two Suction Hoses  
Pre-Filter  
HEPA Filter  
Carbon Filter  
Power Cord



#### Orderable Part Numbers

Part Number	Description
CQ-FE-2	High Flow Fume Extractor, 3 Filter Stages, Low Noise (<55dB), 2 Suction Hoses
CQ-FE-2-P3	Pre-Filters (3 Pack) for High Flow Fume Extractor
CQ-FE-2-PHC	Replacement Filter Set (3 Filter Stages) for High Flow Fume Extractor

#### Product Images of Orderable Part Numbers:



CQ-FE-2



CQ-FE-2-P3



CQ-FE-2-PHC

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Chip Quik:](#)

[CQ-FE-2](#)