

Specifications

Materials
 Conductor: Tinned Copper
 Insulation: Flame retardant polyester, White
 Supporting Tape: Polyester, Blue

Electrical
 Voltage Rating: 60V
 Current Rating: 0.5mm pitch=0.5A
 1.0mm pitch=1A


Mechanical & Environmental
 Operating Temperature: 80°C (UL20624)
 105°C (UL20706)

Durability: 30 Cycles

Notes
 For tolerance information, contact GCT

For non-standard options, contact GCT

- Exposed conductor length
- Support strip length
- Conductor thickness/width
- Folding/bending to an angle



Support Strip and Plating Options by Pitch			
Pitch (mm)	Support Strip Length (mm)	Plating Options (conductor thickness x width (mm))	
		Tin	Gold
0.5	6	0.035 x 0.3 (A)	0.035 x 0.3 (A)
1.0	8	0.035 x 0.65 (D)	0.035 x 0.65 (D)
		0.05 x 0.65 (E)	0.05 x 0.65 (E)
		0.1 x 0.65 (C)	0.05 x 0.65 (E)

See Shielded FFC drawing for shielding options

Part Number N/A		Product Description Flat Flex Cable Ordering Information	
Drawing Date 23rd May 2011			
By CC	Tolerances (Except as Noted) Length	Units: Metric (mm)	
Detail FFC CABLE B PCN	Angle		
Revision B1			
Date 30/06/23			
This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE		 www.gct.co	
Not to Scale	Drawn By SA	Sheet No. 1/1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GCT:](#)

[05-26-D-0030-C-4-08-4-T](#) [05-26-D-0050-C-4-08-4-T](#) [05-26-D-0076-C-4-08-4-T](#) [05-26-D-0101-C-4-08-4-T](#) [05-26-D-0127-C-4-08-4-T](#) [05-26-D-0152-C-4-08-4-T](#) [05-26-D-0177-C-4-08-4-T](#) [05-26-D-0203-C-4-08-4-T](#) [05-26-D-0228-C-4-08-4-T](#) [05-26-D-0254-C-4-08-4-T](#) [05-26-D-0279-C-4-08-4-T](#) [05-26-D-0304-C-4-08-4-T](#) [05-30-D-0030-C-4-08-4-T](#) [05-30-D-0050-C-4-08-4-T](#) [05-30-D-0076-C-4-08-4-T](#) [05-30-D-0101-C-4-08-4-T](#) [05-30-D-0127-C-4-08-4-T](#) [05-30-D-0152-C-4-08-4-T](#) [05-30-D-0177-C-4-08-4-T](#) [05-30-D-0203-C-4-08-4-T](#) [05-30-D-0228-C-4-08-4-T](#) [05-30-D-0254-C-4-08-4-T](#) [05-30-D-0279-C-4-08-4-T](#) [05-30-D-0304-C-4-08-4-T](#) [05-40-D-0030-C-4-08-4-T](#) [05-40-D-0050-C-4-08-4-T](#) [05-40-D-0076-C-4-08-4-T](#) [05-40-D-0101-C-4-08-4-T](#) [05-40-D-0127-C-4-08-4-T](#) [05-40-D-0152-C-4-08-4-T](#) [05-40-D-0177-C-4-08-4-T](#) [05-40-D-0203-C-4-08-4-T](#) [05-40-D-0228-C-4-08-4-T](#) [05-40-D-0254-C-4-08-4-T](#) [05-40-D-0279-C-4-08-4-T](#) [05-40-D-0304-C-4-08-4-T](#) [10-04-A-0030-C-4-08-4-T](#) [10-04-A-0050-C-4-08-4-T](#) [10-04-A-0076-C-4-08-4-T](#) [10-04-A-0101-C-4-08-4-T](#) [10-04-A-0127-C-4-08-4-T](#) [10-04-A-0152-C-4-08-4-T](#) [10-04-A-0177-C-4-08-4-T](#) [10-04-A-0203-C-4-08-4-T](#) [10-04-A-0228-C-4-08-4-T](#) [10-04-A-0254-C-4-08-4-T](#) [10-04-A-0279-C-4-08-4-T](#) [10-04-A-0304-C-4-08-4-T](#) [10-04-D-0030-C-4-08-4-T](#) [10-04-D-0050-C-4-08-4-T](#) [10-04-D-0076-C-4-08-4-T](#) [10-04-D-0101-C-4-08-4-T](#) [10-04-D-0127-C-4-08-4-T](#) [10-04-D-0152-C-4-08-4-T](#) [10-04-D-0177-C-4-08-4-T](#) [10-04-D-0203-C-4-08-4-T](#) [10-04-D-0228-C-4-08-4-T](#) [10-04-D-0254-C-4-08-4-T](#) [10-04-D-0279-C-4-08-4-T](#) [10-04-D-0304-C-4-08-4-T](#) [10-05-A-0030-C-4-08-4-T](#) [10-05-A-0050-C-4-08-4-T](#) [10-05-A-0076-C-4-08-4-T](#) [10-05-A-0101-C-4-08-4-T](#) [10-05-A-0127-C-4-08-4-T](#) [10-05-A-0152-C-4-08-4-T](#) [10-05-A-0177-C-4-08-4-T](#) [10-05-A-0203-C-4-08-4-T](#) [10-05-A-0228-C-4-08-4-T](#) [10-05-A-0254-C-4-08-4-T](#) [10-05-A-0279-C-4-08-4-T](#) [10-05-A-0304-C-4-08-4-T](#) [10-05-D-0030-C-4-08-4-T](#) [10-05-D-0050-C-4-08-4-T](#) [10-05-D-0076-C-4-08-4-T](#) [10-05-D-0101-C-4-08-4-T](#) [10-05-D-0127-C-4-08-4-T](#) [10-05-D-0152-C-4-08-4-T](#) [10-05-D-0177-C-4-08-4-T](#) [10-05-D-0203-C-4-08-4-T](#) [10-05-D-0228-C-4-08-4-T](#) [10-05-D-0254-C-4-08-4-T](#) [10-05-D-0279-C-4-08-4-T](#) [10-05-D-0304-C-4-08-4-T](#) [10-06-A-0030-C-4-08-4-T](#) [10-06-A-0050-C-4-08-4-T](#) [10-06-A-0076-C-4-08-4-T](#) [10-06-A-0101-C-4-08-4-T](#) [10-06-A-0127-C-4-08-4-T](#) [10-06-A-0152-C-4-08-4-T](#) [10-06-A-0177-C-4-08-4-T](#) [10-06-A-0203-C-4-08-4-T](#) [10-06-A-0228-C-4-08-4-T](#) [10-06-A-0254-C-4-08-4-T](#) [10-06-A-0279-C-4-08-4-T](#) [10-06-A-0304-C-4-08-4-T](#) [10-06-D-0030-C-4-08-4-T](#) [10-06-D-0050-C-4-08-4-T](#) [10-06-D-0076-C-4-08-4-T](#) [10-06-D-0101-C-4-08-4-T](#)