

## DisplayPort Extension Cable with Latch, 4K @ 60 Hz, HDCP 2.2 (M/F), 6 ft. (1.83 m)

MODEL NUMBER: **P579-006**

### Highlights

- Digital Video and Audio in one cable
- Supports 1080p resolution
- Small footprint compared to VGA or DVI

### Package Includes

DisplayPort Monitor Extension Cable - 6-ft.

### Features

- The future standard for Digital Video and Audio connections
- Supports Displayport v1.2
- Supports High Definition Content Protection (HDCP)

## Specifications

| OVERVIEW                       |                         |
|--------------------------------|-------------------------|
| UPC Code                       | 037332185839            |
| Product Type                   | Passive Cable           |
| Technology                     | DisplayPort             |
| Cable Type                     | Passive                 |
| VIDEO                          |                         |
| Max Supported Video Resolution | 3840 x 2160 (4K) @ 60Hz |
| CONNECTIONS                    |                         |
| Side A - Connector 1           | DISPLAYPORT (MALE)      |
| Side B - Connector 1           | DISPLAYPORT (FEMALE)    |
| Latching or Gripping Connector | Yes                     |
| PHYSICAL                       |                         |
| Color                          | Black                   |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                               |
|--------------------------------------|-------------------------------|
| Cable Jacket Color                   | Black                         |
| Cable Length (ft.)                   | 6                             |
| Cable Length (m)                     | 1.83                          |
| Cable Length (in.)                   | 72                            |
| Shipping Dimensions (hwd / in.)      | 9.00 x 7.00 x 0.50            |
| Shipping Dimensions (hwd / cm)       | 22.86 x 17.78 x 1.27          |
| Shipping Weight (lbs.)               | 0.23                          |
| Shipping Weight (kg)                 | 0.11                          |
| <b>ENVIRONMENTAL</b>                 |                               |
| Operating Temperature Range          | -4° to 140°F (-20° to 60°C)   |
| Storage Temperature Range            | 5° to 122°F (-15° to 50°C)    |
| Relative Humidity                    | 10% to 80% RH, Non-Condensing |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                               |
| IP68 Rated                           | No                            |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                               |
| Product Compliance                   | RoHS                          |
| <b>WARRANTY &amp; SUPPORT</b>        |                               |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty     |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite](#):

[P579-006](#)