

RECEPTACLE: NKRP-2B4-025-225-TH00  
XXXX-XXX-XXX-XXX-XXXX-XXX

### SERIES

NKRP .025" Metal PC Board Mounted Connector

### BODY

2 2-Row

#### BODY STYLE:

B Receptacle, vertical SMT, rear panel mount with fluorosilicone o-ring

#### BODY MATERIAL:

4 Liquid Crystal Polymer w/ stainless steel shell

### SIZE

XXX Number of contacts (009, 015, 021, 025, 031, 037, 051, 065, 069, 085 or 091)

### CONTACTS

#### TYPE CONTACTS/TERMINATIONS:

22 Socket, SMT

#### PLATING OPTIONS:

5 50 u" Au contacts; Sn/Pb alloy terminations ☒  
8 50 u" Au contacts; Tin plated terminations

### HARDWARE

#### STYLE OF HARDWARE:

TH Threaded hole, #0-80 UNF\*

#### WIRING OPTIONS:

00 None

### OPTIONS

EMI EMI o-ring (in lieu of fluorosilicone o-ring)

\* = #2-56 UNC thread on 85, 91 position connectors

Recommended torque value 1.0 inch-lbs. max. (#0-80 thread)

Recommended torque value 2.0 inch-lbs. max. (#2-56 thread)

☒ = Option not RoHS compliant