

PLUG: WT 8 PD9  
 RECEPTACLE: WT 8 SAC  
 XX X XXX

**PLUG**

**RECEPTACLE**

**SERIES**

WT Plug, straight, no mounting ears | WT Receptacle, straight, no mounting ears

**SIZE**

Number of contacts (3 thru 22) | Number of contacts (3 thru 22)

**CONTACTS**

**TYPE CONTACTS/TERMINATIONS:**  
 PC Pin, straight, solder cup (.035" I.D.)  
 PD7 Pin, straight, dip solder, .109" x .027" dia  
 PD9 Pin, straight, dip solder, .140" x .027" dia  
 PD11 Pin, straight, dip solder, .172" x .027" dia  
 PF3 Pin, straight, flex circuit, .050"  
 PF6 Pin, straight, flex circuit, .093"  
 PW40 Pin, straight, wire wrap®, .625"

**TYPE CONTACTS/TERMINATIONS:**  
 SAC Socket, straight, solder cup (.035" I.D.)  
 SAD7 Socket, straight, dip solder, .109" x .027" dia  
 SAD9 Socket, straight, dip solder, .140" x .027" dia  
 SAD11 Socket, straight, dip solder, .172" x .027" dia  
 SAD15 Socket, straight, dip solder, .234" x .027" dia  
 SAF3 Socket, straight, flex circuit, .050"  
 SAF6 Socket, straight, flex circuit, .093"  
 SAG7 Socket, straight, dip solder, .109" x .018" dia  
 SAG9 Socket, straight, dip solder, .140" x .018" dia  
 SAG11 Socket, straight, dip solder, .172" x .018" dia  
 SAP Socket, straight, pin termination, .150" (connector saver)  
 SAR4 Socket, right angle, dip solder, .062" x .025" dia  
 SAR7 Socket, right angle, dip solder, .109" x .025" dia  
 SAR9 Socket, right angle, dip solder, .140" x .025" dia  
 SARC Socket, right angle, solder cup  
 SAW40 Socket, straight, wire wrap®, .625"

**OPTIONS**

- Option Codes: Add to the end of the part number. Example: WT10PC443-1. Call factory for additional codes.
- 443 Polarizing pin installed in contact position noted by dash number. See "Polarization" in Accessories section.
- 444 Contact position noted by dash number is left open (to mate with -443). See "Polarization" in Accessories section.
- B82 Termination face sealed against conformal coating
- CD Cross drilled connector for hold down screws. See page W-13. Example: WT8PCCD or WT8SACCD.
- D01 Pretinned contact terminations (except solder cups, wire wraps® and flex contacts) with 63/37 or 60/40 solder.
- P39 Pretinned contact terminations (except solder cups, wire wraps® and flex contacts) with SAC305 solder (lead free).
- D54 Combine -B82 & -D01 options
- G69 Solder cups fixed in an outward orientation (otherwise contacts will rotate)

Note: The thin outboard barriers are often removed at the factory due to their fragile nature.

= Option not RoHS compliant

DIMENSIONS		
SIZE	A	B
3	.296	.200
4	.396	.300
5	.496	.400
6	.596	.500
7	.696	.600
8	.796	.700
9	.896	.800
10	.996	.900
11	1.096	1.000
12	1.196	1.100
13	1.296	1.200
14	1.396	1.300
15	1.496	1.400
16	1.596	1.500
17	1.696	1.600
18	1.796	1.700
19	1.896	1.800
20	1.996	1.900
21	2.096	2.000
22	2.196	2.100

DIMENSIONS (CD)			
SIZE	# OF CONTACTS	C	D
5	1	.496	—
6	2	.596	.100
7	3	.696	.200
8	4	.796	.300
9	5	.896	.400
10	6	.996	.500
11	7	1.096	.600
12	8	1.196	.700
13	9	1.296	.800
14	10	1.396	.900
15	11	1.496	1.000
16	12	1.596	1.100
17	13	1.696	1.200
18	14	1.796	1.300
19	15	1.896	1.400
20	16	1.996	1.500
21	17	2.096	1.600
22	18	2.196	1.700