



MAN0520

Mini-ITX SBC with LGA1151 9th/8th Gen Intel® Core™ i7/i5/i3 Processor, Dual DisplayPort++, HDMI, LVDS, USB 3.0, mSATA, M.2, and Dual GbE LAN



▲ Side view



Triple-View



DDR4



M.2



PCIe Mini

Features

- LGA1151 9th/8th gen Intel® Core™ i7/i5/i3 processor
- Intel® H310 chipset
- 2 DDR4 SO-DIMM for up to 32GB of memory
- 4 USB 3.0 and 4 USB 2.0
- 4 COM ports
- 3 SATA-600 and 1 mSATA
- PCIe x16 and M.2 Key E

Specifications

Core System

CPU	LGA1151 9th/8th gen Intel® Core™ i7/i5/i3, Intel® Pentium® processors Gold/Celeron® processors (up to 65W)
System Memory	2 x 260-pin DDR4-2666/2400 SO-DIMM up to 32GB
Chipset	Intel® H310
BIOS	AMI
SSD	1 x mSATA
Watchdog Timer	255 levels, 1 to 255 sec.
Expansion Interface	1 x PCIe x16 1 x M.2 Key E 22 x 30
Battery Lithium	Lithium 3V/220mAH
Power Input	Standard 12V ATX power 24+4 pin ATX connector AT Mode Auto Power Function supported



Specifications

Display	
Chipset	Intel® integrated Gfx graphic engine
Memory Size	Share system memory
Display Interface	2 x DisplayPort++ 1 x HDMI 1.4b (3840 x 2160 @ 30Hz) 1 x LVDS; 18/24-bit single/dual channel
**H310: dual-view/Q370: triple-view	
I/O	
SATA	3 x SATA-600
Hardware Monitoring	Detect CPU/system temperature, voltage and fan speed
Ethernet	1 x 10/100/1000 Mbps Ethernet with Intel® I210-AT; supports Wake-on-LAN, PXE Boot ROM 1 x 10/100/1000 Mbps Ethernet with Intel® I219-LM; supports Wake-on-LAN, PXE Boot ROM
Audio	HD Codec audio as MIC-in/Line-in/Line-out with Realtek ALC662
USB	4 x USB 3.0 4 x USB 2.0
Serial	1 x RS-232/422/485 (with +5V/+12V power) 3 x RS-232
PS/2 Combo Port	N/A
TPM	Onboard TPM 2.0 (optional)
SMBus	N/A
Digital I/O	8-channel in/out programmed
Mechanical and Environmental	
Dimensions	170 x 170 mm
Board Thickness	1.6 mm
Operating Temperature	0°C to +60°C (+32°F to +140°F)
Relative Humidity	10% to 95% relative humidity, non-condensing

Ordering Information

Standard	
MANO520PHGGA-H310 (P/N: E38M520100)	Mini-ITX SBC with LGA1151 9th/8th gen Intel® Core™ processor, Intel® H310, DisplayPort++, HDMI, LVDS, 2 GbE LAN, and HD Audio; bulk packing
MANO520PHGGA-H310 (P/N: E38M520101)	Mini-ITX SBC with LGA1151 9th/8th gen Intel® Core™ processor, Intel® H310, DisplayPort++, HDMI, LVDS, 2 GbE LAN, and HD Audio; single box
Optional	
594M5002100E	2 x COM port, P=2.0 mm, L=300 mm
594E8422800E	2 x USB 2.0 wafer cable with bracket, P=2.0, L=180 mm
59384500100E	SBC84500 audio cable with bracket, P=2.0 mm, L=420 mm
713PL76A000E	LGA1156 1.5U cooler
5077L07C000E	LGA1156 1U cooler

Packing List

I/O bracket
