



MAN0526

Mini-ITX SBC with LGA1151 Socket 9th/8th Gen Intel® Core™ Processor, Intel® Q370, HDMI, DisplayPort++, eDP, 2 GbE LAN, and HD Audio



▲ Rear view



▲ Side view



Triple-View



DDR4



M.2

Features

- LGA1151 socket 9th/8th Gen Intel® Core™ i7/i5/i3 processor
- Intel® Q370 chipset
- 2 DDR4 SO-DIMM for up to 32GB of memory
- 4 USB 3.0 and 4 USB 2.0
- 6 COM ports
- 2 SATA-600 and 1 M.2 Key M
- PCIe x16 and M.2 Key E

Specifications

Core System

CPU	LGA1151 socket 9th/8th Gen Intel® Core™ i7/i5/i3, Intel® Pentium® processors Gold/Celeron® processors (up to 65W)
System Memory	2 x 260-pin DDR4-2666/2400 SO-DIMM, up to 32GB
Chipset	Intel® Q370
BIOS	AMI
SSD	1 x M.2 Key M 2242/2260/2280; supports NVMe
Watchdog Timer	255 levels, 1 to 255 sec.
Expansion Interface	1 x PCIe x16 1 x M.2 Key E 2230
Battery Lithium	Lithium 3V/220mAH
Power Input	STD 12V ATX power 24+4 pin ATX connector AT Mode Auto Power function supported

Specifications

Display

Chipset	Intel® integrated Gfx graphic engine
Memory Size	Share system memory
Display Interface	1 x DisplayPort++ 1 x eDP 1 x HDMI

I/O

SATA	2 x SATA-600
Hardware Monitoring	Detect CPU/system temperature, voltage and fan speed
Ethernet	1 x 10/100/1000 Mbps Ethernet with Intel® I211-AT; supports Wake-on-LAN, PXE Boot ROM 1 x 10/100/1000 Mbps Ethernet with Intel® I219-LM; supports Wake-on-LAN, PXE Boot ROM
Audio	HD Codec audio as MIC-in/Line-in/Line-out with Realtek ALC888S
USB	4 x USB 3.0 4 x USB 2.0
Serial	1 x RS-232/422/485 (with +5V/+12V power) 5 x RS-232
TPM	Onboard TPM 2.0
SMBus	N/A
Digital I/O	8-channel programmable input/output

Mechanical and Environmental

Dimensions	170 x 170 mm
Board Thickness	1.6 mm
Operating Temperature	0°C to +60°C (+32°F to +140°F)
Relative Humidity	10% to 95% relative humidity, non-condensing

Packing List

I/O bracket

Ordering Information

Standard

MANO526	Mini-ITX SBC with LGA1151 socket 9th/8th Gen Intel® Core™ processor, Intel® Q370, HDMI, DisplayPort++, eDP, 2 GbE LAN, and HD Audio
---------	---

Optional

59384500200E	COM port x 2 cable w/ bracket P=2.0, L=250 mm
594E8422800E	2 x USB 2.0 wafer cable with bracket, P=2.0, L=180 mm
713PL76A000E	LGA1156 1.5U, H=36.5