


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

1	2	3	4
Item No.	Part No.	Description	
1	SPNI-001T-P0.5	PNI Connector Male Contact	
2	UL1061, 22 AWG	Black	

Electrical Specifications
Current: 3.0AAC/DC
Voltage: 100V AC/DC

APPLICABLE HOUSINGS			
NO. OF CIRCUITS	SOCKET HOUSINGS (FOR MALE CONTACT)		OPTIONAL RETAINER
	WITHOUT PANEL LOCKS	WITH PANEL LOCKS	
2	PNIRR-02VF	PNIRR-02V	PNIS-02V
3	PNIRR-03VF	PNIRR-03V	PNIS-03V
4	PNIRR-04VF	PNIRR-04V	PNIS-04V
5	PNIRR-05VF	PNIRR-05V	PNIS-05V
6	PNIRR-06VF	PNIRR-06V	PNIS-06V
8	PNIRR-08VF	PNIRR-08V	PNIS-08V
10	PNIRR-10VF	PNIRR-10V	PNIS-10V



ZONE	REV	DESCRIPTION	DATE	APPROVED
	1	Add Electrical Specifications	7/02/2018	LM

All dimensions are in millimeters with a default tolerance of +/- 5.0 unless otherwise specified.					CUSTOMER NAME			
Drawn By: Larissa Mosley					DESCRIPTION			
Checked By: Steven Pilkington					2.0mm Pitch PNI Series Standard Leads - 4" Inside Length DOUBLE END LEADS, M-M			
SCALE 1:1		DRAWING NO. GAM-355		DATE 5/8/2018		PART NO. ASPNISPN122K102		
						REV		