


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

Item No.	Part No.	Description
1	RARSFP-1V-00 & RARSFC-1V	1 POS Right-Angle RSF Housing & Cover
1	RASRSF-61T-250A	Right-Angle RSF Terminal - Brass Tin-Plated
2	UL1015, 16 AWG	Black

Electrical Specifications
Current: 15AAC/DC
Voltage: 250V AC/DC



All dimensions are in millimeters with a default tolerance of +/- 5.0 unless otherwise specified.		CUSTOMER NAME	
		DESCRIPTION	
8" INSIDIE LENGTH - 1 POSITION, LIF, POS LOCK, 250, FLAG, SINGLE-END ASSY, BRASS TIN-PLATED BLUNT LEAD, F		SIZE	REV
Customer Part No.	Part No.	A01RARSFP16K203B	
SCALE 1:1	DRAWING NO. GAM-511	DATE 6/15/2018	

ZONE	REV	DESCRIPTION	DATE	APPROVED
	1	Add Electrical Specifications	7/03/2018	LM