


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

Item No.	Part No.	Description
1	SXNI-001T-P0.6	XNI Connector Female Contact
2	UL1007, 22 AWG	Black

Electrical Specifications

Current: 3.0AAC/DC

Voltage: 250V AC/DC



APPLICABLE HOUSINGS

NO. OF CIRCUITS	HOUSING PART NO.
2	XNIRP-02V-A-S
3	XNIRP-03V-A-S
4	XNIRP-04V-A-S
5	XNIRP-05V-A-S
6	XNIRP-06V-A-S
7	XNIRP-07V-A-S
8	XNIRP-08V-A-S
9	XNIRP-09V-A-S
10	XNIRP-10V-A-S
11	XNIRP-11V-A-S
15	XNIRP-15V-A-S

JST

ZONE	REV	DESCRIPTION	DATE	APPROVED
1	1	Add Electrical Specifications	7/02/2018	LM

All dimensions are in millimeters with a default tolerance of +/- 5.0 unless otherwise specified.		CUSTOMER NAME		
		DESCRIPTION		
2.5mm Pitch XNI Series Standard Leads - 4" Inside Length DOUBLE END LEADS		SIZE	CUSTOMER PART NO.	PART NO.
Drawn By: Larissa Mosley		SCALE	1:1	ASXNISXNI22K102
Checked By: Steven Pilkington		DRAWING NO. GAM-373	DATE 5/14/2018	REV