


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

1	2	3	4
Item No.	Part No.	Description	
1	SGHD-002T-C0.2A	GHD Connector Contact	
2	UL1061, 26 AWG	Black	

Electrical Specifications
Current: 1.25A AC/DC
Voltage: 50V AC/DC

APPLICABLE HOUSINGS	
NO. OF CIRCUITS	HOUSING PART NO.
10	GHDR-10V-S-1 (F)
12	GHDR-12V-S-1 (F)
14	GHDR-14V-S-1 (F)
16	GHDR-16V-S-1 (F)
18	GHDR-18V-S-1 (F)
20	GHDR-20V-S-1 (F)
22	GHDR-22V-S-1 (F)
24	GHDR-24V-S-1 (F)
26	GHDR-26V-S-1 (F)
28	GHDR-28V-S-1 (F)
30	GHDR-30V-S-1 (F)
32	GHDR-32V-S-1 (F)
34	GHDR-34V-S-1 (F)
36	GHDR-36V-S-1 (F)
38	GHDR-38V-S-1 (F)
40	GHDR-40V-S-1 (F)



JST

ZONE	REV	DESCRIPTION	DATE	APPROVED
1				
2				
3				
4				
5				
6				
7				
8				

All dimensions are in millimeters with a default tolerance of +/- 5.0 unless otherwise specified.	CUSTOMER NAME		
	DESCRIPTION		
1.25mm Pitch GHD Series Standard Leads - 4" Inside Length DOUBLE END LEADS		SIZE	
Drawn By: Larissa Mosley		CUSTOMER PART NO.	PART NO.
Checked By: Steven Pilkington		AGHDGHD26K102	
SCALE 1:1		DRAWING NO. GAM-694	DATE 1/24/2019