



NOTES:
1. ALLOWABLE CUT LENGTH IN 0.25" INCREMENTS.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	ENGINEERING RELEASE	4/20/2012	T.Y.
B	ECO-1267: UPDATED COMPONENT DIMENSIONS	6/26/2024	A.V.
C	ECO-1274: UPDATED MFG DRAWING	7/10/2024	A.V.




EXAMPLE:

PM7-C2031-6.50
SERIES FIBER LENGTH IN 0.25" INCREMENTS



LENGTH (L)	TOLERANCE
2.50" ~ 16.00"	±0.05"
16.25" ~ 40.00"	±0.15"
40.25" ~ 80.00"	±0.30"
80.25" ~ 3,940.0"	±0.5%

CUSTOMER USE DRAWING

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		BIVAR [®] 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°		
.XX ± .02			
.XXX ± .010		TITLE: 7mm Circular Lens Flexible Light Pipe FLPS2031 Indicators	
DESIGNED: T. YIN	DATE: 4/20/2012	DRAWING NO: PM7-C2031-XX.XX	REVISION: C
REVISED: K. BARON	DATE: 7/10/2024	SHEET SIZE A	CAGE CODE: 32559
CHECKED: D. ASHBY	DATE: 7/10/2024	SCALE: 2:1	SHEET # 1 OF 1
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING			