

Specification Sheet

Part Number: 102-69067



The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.

Bundling Clip with Arrowhead, 1.5" Long, 0.03 - 0.05" Panel Thickness, PA66HIRHS, Black, 500/pkg

Article Number	102-69067
Type	ATSBCKSFT6.5
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.
Short Description	Bundling Clip with Arrowhead, 1.5" Long, 0.03 - 0.05" Panel Thickness, PA66HIRHS, Black, 500/pkg
Global Part Name	ATSBCKSFT6.5-PA66HIRHS-BK
Length L (Imperial)	1.5

Length L (Metric)	39.0
Fixation Method	Arrowhead
Width W (Imperial)	0.354
Width W (Metric)	9.0
Bundle Diameter Max (Imperial)	0.79
Bundle Diameter Max (Metric)	20.0
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.05
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	1.3
Mounting Hole Diameter D (Imperial)	0.25 - 0.26 "
Mounting Hole Diameter D (Metric)	6.3 - 6.7 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.7

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)