

Specification Sheet

Part Number: 104-10000



Cordless operation means less hand strain and no cord to get in the way.

Auto calibration after every cycle means exceptionally consistent performance.

Flush cut nose piece and blade ensure clean, safe cuts.

Metabo CAS 2.0 Ah battery and charger are compatible with several other tool brands.

Article Number 104-10000

Type ProCut 9

Color Blue (BU)

Quantity Per pack

Product Description

The ProCut battery powered cable tie tool system automatically tensions and cuts T50-T250 and wide strap cable ties. A single pull of the trigger does all the work. Its 16 tension settings ensure precision results. Designed for professionals with an ergonomic, soft-grip handle and low-force trigger to reduce hand strain. A secondary trigger button on the rear assists in hard-to-reach applications. The ProCut can produce up to 2,000 cycles per charge utilizing the Metabo CAS battery (also used on our CPK Hybrid tool).

Short Description Procut Tool With Battery, Metal/Plastic, Blue, 1/pkg

Global Part Name

ProCut 9-MET/PL-BU

Tension Setting Tools

Adjustable

Power Supply

CAS Lithium-Ion Battery

Material

Plastic (PL) Metal (MET)

Material Shortcut

MET PL

UV Resistant (Yes/No)

No

Operating Temperature

-40°F to +257°F (-40°C to +125°C)

Reach Compliant (Article 33)

Yes

ROHS Compliant

Yes

Package Quantity (Imperial)

1

Package Quantity (Metric)

1

Customs Number

8467290095

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)