

Specification Sheet

Part Number: MK7P



- Improved compressed air supply for faster tensioning piston movement.
- Glass fiber-reinforced plastic construction makes tool lightweight yet tough.
- Automatic ejection of cut-off cable tie end speeds production.
- Three-level preset control to set tool tension.
- Optional safety cap prevents tension setting from being changed by accident (important when bundling sensitive materials and maintaining process reliability).

MK7P Pneumatic Tool, Plastic Housing, 1/Pkg

Article Number	110-07101
Type	MK7P
Color	Black (BK)
Quantity Per	pack
Product Description	The Mark 7 Pneumatic (MK7P) industrial-grade cable tie application tool is built to perform in demanding production and manufacturing environments. Heavy duty precision parts ensure repeatability in the tensioning process. The MK7P is ergonomically designed for operator comfort, reducing hand, arm and wrist fatigue. It consistently maintains the correct tension and provides a flush, safe cut-off with no sharp edges.
Short Description	MK7P Pneumatic Tool, Plastic Housing, 1/Pkg

Global Part Name	MK7P-PA66GF30-BK
Length L (Metric)	220
Width W (Metric)	40
Cable Ties	T18 thru T50 Series CTT20 thru CTT60
Cycle Time	4 strokes per second
Height H (Metric)	170
Tension Setting Tools	Adjustable
Cable Tie Width Max (Imperial)	0.18
Power Supply	Dry or lubricated air
Tension Force	60-170
Material	Polyamide 6.6, glass fiber reinforced (PA66GF30%)
Material Shortcut	PA66GF30
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Reach Compliant (Article 33)	No

ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8467195090

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)