

Specification Sheet

Part Number: MK9P-109

Enhanced technology for better application of cable ties.

Improved compressed air supply for faster tensioning piston movement.

Shorter processing time and greater volume of connecting tie application.

Genuine potential for rationalization.

Ergonomic design, molded handle to prevent slippage, reduce operator fatigue.

Lightweight but very tough housing made of glass fiber-reinforced plastic.

Meets high industry standards.

Tensioning and cutting off cable ties flush with head by pressing one button.

Smooth cut edge to prevent injuries.

Automatic ejection of cut-off cable tie end.

Three-level preset control to set tool tension.

Optional safety cap to prevent tension setting from being changed by accident (important when bundling sensitive materials and maintaining process reliability.)

Non-slip, comfortable grip, soft touch trigger, and one-touch tensioning/cut off.

Very lightweight and easy to use on all cable ties 2.5–4.8 mm wide.

All separately sold accessories are compatible with the MK7P series tool.



MK9P Replacement Blade, 1/Pkg

Article Number	110-09111
Type	SP MK9P replacement blade
Color	Metal (ML)
Quantity Per	pack
Product Description	Replacement Blade
Short Description	MK9P Replacement Blade, 1/Pkg
Global Part Name	SP MK9P replacement blade-MET-ML
Length L (Metric)	280
Width W (Metric)	55
Height H (Metric)	200
Tension Setting Tools	Adjustable
Material	Metal (MET)
Material Shortcut	MET
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8208900000

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)