

Specification Sheet

Part Number: 110-77004

Cuts ties from 18 to 80 lb with a clean, flush cut for personnel safety and wire insulation integrity.

Quality construction with impact-resistant housing, tested at over 1 million cycles, provides high durability resulting in fewer repairs and an extended product life.

Lightweight tool with the most technologically advanced ergonomic design for reducing work-related risks such as fatigue and injury that affect productivity.

Tension dial offers 33 precise, easy-to-read settings that reduce subjectivity or the need for fine tuning.

Tension lock-in mechanism prevents operator from changing tension setting during critical applications.



Article Number 110-77004

Type EVO7iSP

Color Blue (BU) Black (BK)

Quantity Per box

Product Description	HellermannTyton's EVO 7i industrial-grade, mechanical hand tool is ergonomically designed to reduce the risks of repetitive stress injuries to operators while simultaneously increasing productivity. The EVO 7i's Tension/Lock/Cut Technology delivers performance, safety and comfort for operators. Calibrated tensioning assures consistent wire bundle tension before flush cut-off. Available in a standard grip span (EVO 7i) or short grip span (EVO 7iSP) for smaller hands. Additional accessories are available.
Short Description	EVO 7iSP Mechanical Hand Tool, Tension Range 4 - 37 lb, Short Hand Span, 1/pkg
Global Part Name	EVO7iSP-MET/PL-BK/BU
Length L (Imperial)	7.5
Length L (Metric)	192
Tension Setting Tools	Adjustable
Material	Metal (MET) Plastic (PL)
Material Shortcut	MET PL
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1

Package Quantity (Metric) 1

Customs Number 8205599000

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)