

Specification Sheet

Part Number: MK9SST



Glass fiber reinforced housing for extra durability.

Ergonomic design protects against repetitive strain injuries.

Calibrated for consistent tensioning and cutting of MBT-series metal ties.

MK9 Stainless Steel Tie Tensioning and Cut-Off Tool, PL/GF, Gray, 1/pkg

Article Number 110-95000

Type MK9SST

Color Gray (GY)

Quantity Per pack

Product Description With its lightweight, ergonomic design, the MK9SST is an ideal tool for applying MBT-series stainless steel cable ties. As tough as these ties are, the MK9SST cuts and tensions without operator fatigue or strain. Tensioning is fully adjustable using a quick, two-level control with an additional fine setting. This avoids damage to bundles. Cable ties are cut off automatically flush with the head when the preset tensioning level has been reached.

Short Description MK9 Stainless Steel Tie Tensioning and Cut-Off Tool, PL/GF, Gray, 1/pkg

Global Part Name	MK9SST-PA66GF30-GY
Cable Ties	All MBT Series for both 304 and 316 materials
Tension Setting Tools	Adjustable
Cable Tie Width Max (Imperial)	0.6
Material	Polyamide 6.6, glass fiber reinforced (PA66GF30%)
Material Shortcut	PA66GF30
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8205599000

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)