

Specification Sheet

Part Number: T30LL0M4



- Engineered and manufactured for maximum performance and quality.
- Made from 100% high-quality plastic to ensure efficient recycling.
- Inside serration for a strong grip onto bundles.
- Easy application either manually or with a tensioning tool.
- Bent tail allows for simpler insertion.

Cable Tie, 11" Long, UL Rated, 30lb Tensile Strength, PA66, Black, 1000/pkg

|                     |                                                                                                                                                                                                                                                                                                                                                              |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 111-03511                                                                                                                                                                                                                                                                                                                                                    |
| Type                | T30LL                                                                                                                                                                                                                                                                                                                                                        |
| Color               | Black (BK)                                                                                                                                                                                                                                                                                                                                                   |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                                                                                         |
| Product Description | T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation. |
| Short Description   | Cable Tie, 11" Long, UL Rated, 30lb Tensile Strength, PA66, Black, 1000/pkg                                                                                                                                                                                                                                                                                  |

|                  |               |
|------------------|---------------|
| Global Part Name | T30LL-PA66-BK |
|------------------|---------------|

|                                     |    |
|-------------------------------------|----|
| Minimum Tensile Strength (Imperial) | 30 |
|-------------------------------------|----|

|                                   |     |
|-----------------------------------|-----|
| Minimum Tensile Strength (Metric) | 135 |
|-----------------------------------|-----|

|                     |      |
|---------------------|------|
| Length L (Imperial) | 11.0 |
|---------------------|------|

|                   |       |
|-------------------|-------|
| Length L (Metric) | 290.0 |
|-------------------|-------|

|                               |      |
|-------------------------------|------|
| Identification Plate Position | none |
|-------------------------------|------|

|                    |    |
|--------------------|----|
| Releasable Closure | No |
|--------------------|----|

|             |              |
|-------------|--------------|
| Tie Closure | plastic pawl |
|-------------|--------------|

|         |                 |
|---------|-----------------|
| Variant | Inside Serrated |
|---------|-----------------|

|                    |      |
|--------------------|------|
| Width W (Imperial) | 0.14 |
|--------------------|------|

|                  |     |
|------------------|-----|
| Width W (Metric) | 3.6 |
|------------------|-----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Min (Imperial) | 0.06 |
|--------------------------------|------|

|                              |     |
|------------------------------|-----|
| Bundle Diameter Min (Metric) | 1.5 |
|------------------------------|-----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Max (Imperial) | 3.15 |
|--------------------------------|------|

|                              |      |
|------------------------------|------|
| Bundle Diameter Max (Metric) | 80.0 |
|------------------------------|------|

|                      |     |
|----------------------|-----|
| Thickness T (Metric) | 1.2 |
|----------------------|-----|

|                               |                                  |
|-------------------------------|----------------------------------|
| Material                      | Polyamide 6.6 (PA66)             |
| Material Shortcut             | PA66                             |
| Flammability                  | UL 94 V-2                        |
| Halogen Free                  | Yes                              |
| UV Resistant (Yes/No)         | No                               |
| Use Conditions                | For Indoor and Outdoor Use       |
| Plenum Rating                 | AH-2                             |
| Operating Temperature         | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33)  | Yes                              |
| ROHS Compliant                | Yes                              |
| Certification/Specification   | UL 62275                         |
| UL Recognized (US)            | Yes                              |
| UL Listed (US and Canada)     | Yes                              |
| UL Recognized (US and Canada) | Yes                              |
| UL Listed (US)                | Yes                              |

|                             |            |
|-----------------------------|------------|
| Package Quantity (Imperial) | 1000       |
| Package Quantity (Metric)   | 1000       |
| Customs Number              | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)