

Specification Sheet

Part Number: 111-15422

Engineered and manufactured for maximum performance and quality.

Made from 100% high-quality plastic to ensure efficient recycling.

Inside serration for a strong grip onto bundles.

Easy application either manually or with a tensioning tool.

Complies with MS3367-6-9, Class 2 and SAE-AS33671.



Heavy Duty MilSpec Cable Tie, 32" Long, MS3367, 175lb Tensile Strength, PA66, Natural, 25/bg

Article Number	111-15422
----------------	-----------

Type	T150L
------	-------

Color	Natural (NA)
-------	--------------

Quantity Per	pack
--------------	------

Product Description	Heavy duty T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation. Specially manufactured to comply with Military Specification MS3367-6-9, Class 2 and SAE-AS33671.
---------------------	---

Short Description	Heavy Duty MilSpec Cable Tie, 32" Long, MS3367, 175lb Tensile Strength, PA66, Natural, 25/bg
Global Part Name	T150L-PA66-NA
Minimum Tensile Strength (Imperial)	175
Minimum Tensile Strength (Metric)	780
Length L (Imperial)	32.3
Length L (Metric)	820.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.35
Width W (Metric)	8.9
Bundle Diameter Min (Imperial)	0.31
Bundle Diameter Min (Metric)	8.0
Bundle Diameter Max (Imperial)	9.65
Bundle Diameter Max (Metric)	245.0

Thickness T (Imperial)	0.07
Thickness T (Metric)	1.9
Cable Tie Head Length (Imperial)	0.51
Cable Tie Head Width (Imperial)	0.55
Height H (Imperial)	0.37
Height H (Metric)	9.5
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
US MIL SPEC	MS3367-6-9, Class 2 SAE-AS33671
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Plenum Rating	AH-2
Operating Temperature	-40°F to +185°F (-40°C to +85°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 62275
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com