

Specification Sheet

Part Number: 111-85460



Wing design helps stabilize the tie in high vibration applications

Includes a ladder type strap as opposed to a conventional serrated strap; providing the benefit of being extra flexible.

Design of tie provides low insertion and high extraction force.

1-Piece Cable Tie with Arrowhead Mount with Wings, 6.5"L, 50lb, 0.25 - 0.3" Hole Dia, PA66, Black, 500/bg

Article Number	111-85460
----------------	-----------

Type	T50SL6
------	--------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.
---------------------	--

Short Description	1-Piece Cable Tie with Arrowhead Mount with Wings, 6.5"L, 50lb, 0.25 - 0.3" Hole Dia, PA66, Black, 500/bg
-------------------	---

Global Part Name	T50SL6-PA66-BK
------------------	----------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	6.5
---------------------	-----

Length L (Metric)	165
-------------------	-----

Fixation Method	Arrowhead
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.5
------------------------------	-----

Bundle Diameter Max (Imperial)	1.34
--------------------------------	------

Bundle Diameter Max (Metric)	34.0
------------------------------	------

Thickness T (Metric)	1.2
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.10
Panel Thickness Min (Metric)	0.5
Panel Thickness Max (Metric)	2.5
Mounting Hole Diameter D (Imperial)	0.25 - 0.3 "
Mounting Hole Diameter D (Metric)	6.3 - 7.5 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.3
Mounting Hole Diameter D Max (Metric)	7.5
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use

Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)