

Specification Sheet

Part Number: T50L9C2

- Engineered and manufactured for maximum performance and quality.
- Made from 100% high-quality plastic to ensure efficient recycling.
- Inside serration for a strong grip onto bundles.
- Easy application either manually or with a tensioning tool.
- Bent tail allows for simpler insertion.



Cable Tie, 15" Long, UL Rated, 50lb Tensile Strength, PA66, Natural, 100/pkg

Article Number	112-05419
Type	T50L
Color	Natural (NA)
Quantity Per	pack
Product Description	T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Cable Tie, 15" Long, UL Rated, 50lb Tensile Strength, PA66, Natural, 100/pkg

Global Part Name	T50L-PA66-NA
------------------	--------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	15.35
---------------------	-------

Length L (Metric)	390.0
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.19
--------------------	------

Width W (Metric)	4.8
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.5
------------------------------	-----

Bundle Diameter Max (Imperial)	4.33
--------------------------------	------

Bundle Diameter Max (Metric)	110.0
------------------------------	-------

Thickness T (Imperial)	0.05
------------------------	------

Thickness T (Metric)	1.2
Cable Tie Head Length (Imperial)	0.28
Cable Tie Head Width (Imperial)	0.32
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Plenum Rating	AH-2
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 62275
UL Recognized (US)	Yes

UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)