

Specification Sheet

Part Number: T50ML0C2



Screw mount style creates low insertion and high extraction force.

Choose from several tensile strengths and lengths to accommodate a range of applications.

1-Piece Cable Tie with Screw Mount, 15.4" Long, #10 Screw, 4.0" Max Bundle Dia, 50lb, PA66, Black, 100/pkg

|                     |                                                                                                                                                                                                      |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 113-00007                                                                                                                                                                                            |
| Type                | T50ML                                                                                                                                                                                                |
| Color               | Black (BK)                                                                                                                                                                                           |
| Quantity Per        | pack                                                                                                                                                                                                 |
| Product Description | 1-piece Screw Mount Cable Ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths. |
| Short Description   | 1-Piece Cable Tie with Screw Mount, 15.4" Long, #10 Screw, 4.0" Max Bundle Dia, 50lb, PA66, Black, 100/pkg                                                                                           |
| Global Part Name    | T50ML-PA66-BK                                                                                                                                                                                        |

|                                     |                 |
|-------------------------------------|-----------------|
| Minimum Tensile Strength (Imperial) | 50              |
| Minimum Tensile Strength (Metric)   | 225             |
| Length L (Imperial)                 | 15.4            |
| Length L (Metric)                   | 390.0           |
| Fixation Method                     | Screw Mount     |
| Identification Plate Position       | none            |
| Releasable Closure                  | No              |
| Tie Closure                         | plastic pawl    |
| Variant                             | Inside Serrated |
| Width W (Imperial)                  | 0.18            |
| Width W (Metric)                    | 4.7             |
| Bundle Diameter Min (Imperial)      | 0.12            |
| Bundle Diameter Min (Metric)        | 3.0             |
| Bundle Diameter Max (Imperial)      | 3.94            |
| Bundle Diameter Max (Metric)        | 100.0           |
| Height H (Imperial)                 | 0.23            |

|                                     |                                  |
|-------------------------------------|----------------------------------|
| Height H (Metric)                   | 5.84                             |
| Mounting Hole Diameter D (Imperial) | 0.22 "                           |
| Mounting Hole Diameter D (Metric)   | 5.5 mm                           |
| Material                            | Polyamide 6.6 (PA66)             |
| Material Shortcut                   | PA66                             |
| Flammability                        | UL 94 V-2                        |
| UV Resistant (Yes/No)               | No                               |
| Use Conditions                      | For Indoor and Outdoor Use       |
| Plenum Rating                       | AH-2                             |
| Operating Temperature               | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33)        | Yes                              |
| ROHS Compliant                      | Yes                              |
| Certification/Specification         | UL 62275                         |
| UL Recognized (US)                  | Yes                              |
| UL Listed (US and Canada)           | Yes                              |

|                               |            |
|-------------------------------|------------|
| UL Recognized (US and Canada) | Yes        |
| UL Listed (US)                | Yes        |
| Package Quantity (Imperial)   | 100        |
| Package Quantity (Metric)     | 100        |
| Customs Number                | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)