

Specification Sheet

Part Number: T50ML9M4



Screw mount style creates low insertion and high extraction force.

Choose from several tensile strengths and lengths to accommodate a range of applications.

1-Piece Cable Tie with Screw Mount, 15.4" Long, #10 Screw, 4.0" Max Bundle Dia, 50lb, PA66, Natural, 1000/pkg

Article Number	113-05403
----------------	-----------

Type	T50ML
------	-------

Color	Natural (NA)
-------	--------------

Quantity Per	pack
--------------	------

Product Description	1-piece Screw Mount Cable Ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths.
---------------------	--

Short Description	1-Piece Cable Tie with Screw Mount, 15.4" Long, #10 Screw, 4.0" Max Bundle Dia, 50lb, PA66, Natural, 1000/pkg
-------------------	---

Global Part Name	T50ML-PA66-NA
------------------	---------------

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	15.4
Length L (Metric)	390.0
Fixation Method	Screw Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.12
Bundle Diameter Min (Metric)	3.0
Bundle Diameter Max (Imperial)	3.94
Bundle Diameter Max (Metric)	100.0
Height H (Imperial)	0.23

Height H (Metric)	5.84
Mounting Hole Diameter D (Imperial)	0.22 "
Mounting Hole Diameter D (Metric)	5.5 mm
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Plenum Rating	AH-2
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 62275
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes

UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)