

Specification Sheet

Part Number: RT150REP0X2



Special design with extended pawl offers a release feature for quick and easy access to wire bundles.

Head design provides high tensile strength with very low insertion force even after repeated use.

Releasable Cable Tie, Release Tab, 15.4" Long, 175lb Tensile Strength, PA66, Black, 25/pkg

Article Number 115-00036

Type RT150REP

Color Black (BK)

Quantity Per pack

Product Description HellermannTyton heavy duty releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Releasable Cable Tie, Release Tab, 15.4" Long, 175lb Tensile Strength, PA66, Black, 25/pkg

Global Part Name RT150REP-PA66-BK

Minimum Tensile Strength (Imperial) 175

Minimum Tensile Strength (Metric) 780

Length L (Imperial) 15.4

Length L (Metric) 390.0

Fixation Method Releasable Cable Tie

Identification Plate Position none

Releasable Closure Yes

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.35

Width W (Metric) 8.8

Bundle Diameter Min (Imperial) 0.31

Bundle Diameter Min (Metric) 8.0

Bundle Diameter Max (Imperial) 4.13

Bundle Diameter Max (Metric) 105.0

Cable Tie Width Max (Imperial)	0.35
Cable Tie Width Max (Metric)	8.8
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)