

Specification Sheet

Part Number: 115-28589



Manufactured from a soft, tear-resistant thermoplastic polyurethane these ties have several unique features: strong, yet elastic, and suitable for temperatures as low as -20 degrees C.

The SOFTFIX ties are releasable and reusable which is ideal for bundling cables in temporary applications such as musical events, theatres etc.

Cable Tie without Serration, 22.83" Long, Flexible TPU, Black, 10/pkg

Article Number 115-28589

Type SRT58028

Color Black (BK)

Quantity Per pack

Product Description Soft, flexible material makes these ties particularly suitable for use on sensitive wires, such as fibre-optic cables. Additionally the ties are suitable for use on moving or vibrating applications. The double slotted head allows for parallel bundling.

Short Description Cable Tie without Serration, 22.83" Long, Flexible TPU, Black, 10/pkg

Global Part Name SRT58028-TPU-BK

Minimum Tensile Strength (Metric)	360
Length L (Imperial)	22.83
Length L (Metric)	580
Fixation Method	Releasable Cable Tie
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	ladder style
Variant	Not Serrated
Width W (Metric)	28.0
Bundle Diameter Max (Imperial)	5.91
Bundle Diameter Max (Metric)	150
Thickness T (Metric)	3.4
Material	Thermoplastic Polyurethane (TPU)
Material Shortcut	TPU
Flammability	UL 94 HB

Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	3926909988
Weight (Metric)	58.2

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)