

Specification Sheet

Part Number: RTT750HR.NX900



The heavy duty Speedy tie features a specially designed head and patented trigger to allow for repeated use in temporary bundling applications.

Additional design feature on the head allows excess strap to be tucked away after installation.

Releasable Cable Tie, 29.6" Long, 200 lb Tensile Strength, PA66, Yellow, 5/pkg

Article Number	115-00001
Type	SpeedyTie (RTT750HR)
Color	Red (RD) Yellow (YE)
Quantity Per	pack
Product Description	HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes or temporary bundling are necessary. The head design guarantees high tensile strength even after repeated use.
Short Description	Releasable Cable Tie, 29.6" Long, 200 lb Tensile Strength, PA66, Yellow, 5/pkg
Global Part Name	SpeedyTie (RTT750HR)-PA66-RD/YE

Minimum Tensile Strength (Imperial)	200
Minimum Tensile Strength (Metric)	888
Length L (Imperial)	29.6
Length L (Metric)	752.0
Fixation Method	Releasable Cable Tie
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.51
Width W (Metric)	13.0
Bundle Diameter Min (Imperial)	1.57
Bundle Diameter Min (Metric)	40.0
Bundle Diameter Max (Imperial)	8.27
Bundle Diameter Max (Metric)	210.0
Thickness T (Imperial)	0.075

Thickness T (Metric)	1.9
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	5
Package Quantity (Metric)	5
Customs Number	3926909988

