

Specification Sheet

Part Number: 115-00054



- Release feature allows maintenance or changeouts as needed.
- Polyamide 6.6 cable ties deliver excellent resistance to chemicals and salts.
- Inside serrations provide strong grip on cables and wire bundles.
- Reliable bundle fastening plus low insertion force for ease of use.

Releasable Cable Tie, Release Lever, 9.8" Long, 50lb Tensile Strength, PA66, Natural, 100/pkg

Article Number	115-00054
Type	RF250
Color	Natural (NA)
Quantity Per	pack
Product Description	Releasable Cable Ties feature an integrated release mechanism on the head, allowing for changeouts without destroying the cable tie. The head design ensures consistently high tensile strength, even after repeated use. Rounded tail glides into head with low insertion force.
Short Description	Releasable Cable Tie, Release Lever, 9.8" Long, 50lb Tensile Strength, PA66, Natural, 100/pkg
Global Part Name	RF250-PA66-NA

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	9.8
Length L (Metric)	250.0
Fixation Method	Releasable Cable Tie
Identification Plate Position	none
Releasable Closure	Yes
Width W (Imperial)	0.29
Width W (Metric)	7.4
Bundle Diameter Min (Imperial)	0.1
Bundle Diameter Min (Metric)	2.5
Bundle Diameter Max (Imperial)	2.83
Bundle Diameter Max (Metric)	72.0
Thickness T (Metric)	1.2
Material	Polyamide 6.6 (PA66)

Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com