

Specification Sheet

Part Number: RT40R0M4



Special design with extended pawl offers a release feature for quick and easy access to wire bundles.

Head design provides high tensile strength with very low insertion force even after repeated use.

Releasable Cable Tie, Release Tab, 8.5" Long, 40 lb Tensile Strength, PA66, Black, 1000/pkg

Article Number	115-06202
Type	RT40R
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Releasable Cable Tie, Release Tab, 8.5" Long, 40 lb Tensile Strength, PA66, Black, 1000/pkg

Global Part Name	RT40R-PA66-BK
Minimum Tensile Strength (Imperial)	40
Minimum Tensile Strength (Metric)	180
Length L (Imperial)	8.5
Length L (Metric)	215.9
Fixation Method	Releasable Cable Tie
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.16
Width W (Metric)	4.0
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	2.01
Bundle Diameter Max (Metric)	51.0

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)