

Specification Sheet

Part Number: 115-11349



Manufactured from a soft, tear-resistant thermoplastic polyurethane these ties have several unique features: strong, yet elastic, and suitable for temperatures as low as -20 degrees C.

The SOFTFIX ties are releasable and reusable which is ideal for bundling cables in temporary applications such as musical events, theatres etc.

Cable Tie without Serration, 13.39" Long, Flexible TPU, Black, 50//pkg

Article Number	115-11349
Type	SRT34011
Color	Black (BK)
Quantity Per	pack
Product Description	Soft, flexible material makes these ties particularly suitable for use on sensitive wires, such as fibre-optic cables. Additionally the ties are suitable for use on moving or and vibrating applications. The double slotted head allows for parallel bundling.
Short Description	Cable Tie without Serration, 13.39" Long, Flexible TPU, Black, 50//pkg
Global Part Name	SRT34011-TPU-BK

Minimum Tensile Strength (Metric)	123
Length L (Imperial)	13.39
Length L (Metric)	340
Fixation Method	Releasable Cable Tie
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	ladder style
Variant	Not Serrated
Width W (Metric)	11.0
Bundle Diameter Max (Imperial)	3.54
Bundle Diameter Max (Metric)	90.0
Thickness T (Metric)	2.3
Material	Thermoplastic Polyurethane (TPU)
Material Shortcut	TPU
Flammability	UL 94 HB

Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988
Weight (Metric)	8.65

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)