

Specification Sheet

Part Number: REZ200.NB3P

The unique, patented head design enables the tie to be inserted through a standard style head for permanent locking or can be twisted into the pinch-releasable style head for easy opening at a later time.

The quick pinch-release mechanism can be released by one hand even when the tie is under tension.



Releasable Cable Tie, 7.9" Long, 30 lb Tensile Strength, PA66, Black, 100/pkg

Article Number	115-40200
----------------	-----------

Type	REZ200
------	--------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
---------------------	---

Short Description	Releasable Cable Tie, 7.9" Long, 30 lb Tensile Strength, PA66, Black, 100/pkg
-------------------	---

Global Part Name	REZ200-PA66-BK
------------------	----------------

Minimum Tensile Strength (Imperial)	30
Minimum Tensile Strength (Metric)	135
Length L (Imperial)	7.9
Length L (Metric)	200
Fixation Method	Releasable Cable Tie
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.19
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.63
Bundle Diameter Min (Metric)	16.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.055

Thickness T (Metric)	1.4
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

