

Specification Sheet

Part Number: 117-00008



Heat stabilized cable ties provide excellent resistance to high heat exposures

Head design contains clamping rails to provide full circumferential compression around bundles

Bent tail allows for quick insertion into head

Double-Head Cable Tie, 15.6" Long, 50lb Tensile Strength, PA66HS, Black, 100/pkg

Article Number	117-00008
----------------	-----------

Type	T50LDH
------	--------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The double head cable tie was designed with a dual locking head to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
---------------------	---

Short Description	Double-Head Cable Tie, 15.6" Long, 50lb Tensile Strength, PA66HS, Black, 100/pkg
-------------------	--

Global Part Name	T50LDH-PA66HS-BK
------------------	------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	15.60
---------------------	-------

Length L (Metric)	395.0
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.19
--------------------	------

Width W (Metric)	4.7
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.6
------------------------------	-----

Bundle Diameter Max (Imperial)	3.94
--------------------------------	------

Bundle Diameter Max (Metric)	100
------------------------------	-----

Bundle Diameter 1st Loop Max (Imperial)	4.0
---	-----

Bundle Diameter 2nd Loop Max (Imperial)	2.0
Thickness T (Imperial)	0.055
Thickness T (Metric)	1.4
Cable Tie Head Length (Imperial)	0.53
Cable Tie Head Width (Imperial)	0.32
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 62275 UL ANSI/UL 1565 UL ANSI/UL 746B

UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)