

Specification Sheet

Part Number: 117-00028



The tie contains a dual locking design to secure two bundles at once.

Head design can also provide spacing between parallel bundles.

Double-Head Cable Tie, 15.7" Long, 120lb Tensile Strength, PA66HIRHS, Orange, 1000/pkg

Article Number	117-00028
----------------	-----------

Type	T120RDH
------	---------

Color	Orange (OG), High Voltage (HV)
-------	--------------------------------

Quantity Per	pack
--------------	------

Product Description	The double head cable tie was designed with a dual locking head to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
---------------------	---

Short Description	Double-Head Cable Tie, 15.7" Long, 120lb Tensile Strength, PA66HIRHS, Orange, 1000/pkg
-------------------	--

Global Part Name	T120RDH-PA66HIRHS-OG
------------------	----------------------

Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	535
Length L (Imperial)	15.7
Length L (Metric)	398.0
Identification Plate Position	none
Releasable Closure	No
Variant	Inside Serrated
Width W (Imperial)	0.30
Width W (Metric)	7.6
Bundle Diameter Min (Imperial)	0.18
Bundle Diameter Min (Metric)	4.6
Bundle Diameter Max (Imperial)	4
Bundle Diameter Max (Metric)	101.6
Bundle Diameter 1st Loop Max (Imperial)	4.0
Bundle Diameter 1st Loop Max (Metric)	101.6
Bundle Diameter 2nd Loop Max (Imperial)	2.0

Bundle Diameter 2nd Loop Max (Metric)	50.8
Height H (Imperial)	0.29
Height H (Metric)	7.5
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)