

Specification Sheet

Part Number: T50RDH0UVC2

The tie contains a dual locking design to secure two bundles at once.

Head design can also provide spacing between parallel bundles.

Bent tail allows for quick insertion into head.



Double-Head Cable Tie, 8.3" Long, 50lb Tensile Strength, PA66UV, Black, 100/pkg

Article Number 117-05011

Type T50RDH

Color Black (BK)

Quantity Per pack

Product Description The double head cable tie was designed with a dual locking head that creates two loops to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Double-Head Cable Tie, 8.3" Long, 50lb Tensile Strength, PA66UV, Black, 100/pkg

Global Part Name T50RDH-PA66UV-BK

Minimum Tensile Strength (Imperial) 50

Minimum Tensile Strength (Metric) 225

Length L (Imperial) 8.30

Length L (Metric) 210.82

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.19

Width W (Metric) 4.7

Bundle Diameter Min (Imperial) 0.06

Bundle Diameter Min (Metric) 1.6

Bundle Diameter Max (Imperial) 1.5

Bundle Diameter Max (Metric) 38.0

Bundle Diameter 1st Loop Max (Imperial) 1.7

Bundle Diameter 1st Loop Max (Metric)	44.4
Bundle Diameter 2nd Loop Max (Imperial)	0.75
Bundle Diameter 2nd Loop Max (Metric)	19.0
Thickness T (Imperial)	0.055
Thickness T (Metric)	1.4
Cable Tie Head Length (Imperial)	0.53
Cable Tie Head Width (Imperial)	0.32

Material Polyamide 6.6 UV-resistant (PA66UV)

Material Shortcut PA66UV

Flammability UL 94 V-2

Halogen Free Yes

UV Resistant (Yes/No) Yes

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +185°F (-40°C to +85°C)

Reach Compliant (Article 33) Yes

ROHS Compliant	Yes
Certification/Specification	UL
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)