

Specification Sheet

Part Number: T50IDH0UVC2



The tie contains a dual locking design to secure two bundles at once.

Head design can also provide spacing between parallel bundles.

Bent tail allows for quick insertion into head.

Double-Head Cable Tie, 12" Long, 50lb Tensile Strength, PA66UV, Black, 100/pkg

Article Number	117-05360
----------------	-----------

Type	T50IDH
------	--------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The double head cable tie was designed with a dual locking head that creates two loops to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
---------------------	--

Short Description	Double-Head Cable Tie, 12" Long, 50lb Tensile Strength, PA66UV, Black, 100/pkg
-------------------	--

Global Part Name	T50IDH-PA66UV-BK
------------------	------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	12.0
---------------------	------

Length L (Metric)	305.0
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.19
--------------------	------

Width W (Metric)	4.7
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.6
------------------------------	-----

Bundle Diameter Max (Imperial)	3
--------------------------------	---

Bundle Diameter Max (Metric)	76.2
------------------------------	------

Bundle Diameter 1st Loop Max (Imperial)	3.0
---	-----

Bundle Diameter 1st Loop Max (Metric)	76.2
Bundle Diameter 2nd Loop Max (Imperial)	1.5
Bundle Diameter 2nd Loop Max (Metric)	38.1
Thickness T (Imperial)	0.055
Thickness T (Metric)	1.4
Material	Polyamide 6.6 UV-resistant (PA66UV)
Material Shortcut	PA66UV
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 1565 UL ANSI/UL 746B UL ANSI/UL 62275

UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)