

Specification Sheet

Part Number: 126-00075



All-in-one bundling and mounting solution reduces costs.

Low-profile design provides dependable cable management in tight spaces.

1-Piece Cable Tie with Arrowhead Mount, 6"L, 50lb Tensile Strength, 5.4mm Round Hole, PA66HS, Black, 500/pkg

Article Number

126-00075

Type

T50SOSKSFT5.4E

Color

Black (BK)

Quantity Per

pack

Product Description

The low-profile push mount design provides an overall shortened length, which assists in limiting protrusion on the opposing side of application surfaces. The mount's rounded tip allows for a smoother surface in case of contact with surrounding components or hands. The dome provides firm, rattle-free performance and keeps out debris. One-piece mounting ties offer a complete solution by both bundling and mounting.

Short Description

1-Piece Cable Tie with Arrowhead Mount, 6"L, 50lb Tensile Strength, 5.4mm Round Hole, PA66HS, Black, 500/pkg

Global Part Name	T50SOSKSFT5.4E-PA66HS-BK
------------------	--------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	180
-----------------------------------	-----

Length L (Imperial)	6.0
---------------------	-----

Length L (Metric)	156.0
-------------------	-------

Fixation Method	Arrowhead
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Outside Serrated
---------	------------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.04
--------------------------------	------

Bundle Diameter Min (Metric)	1.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.38
--------------------------------	------

Bundle Diameter Max (Metric)	35.0
------------------------------	------

Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.05
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	1.3
Mounting Hole Diameter D (Imperial)	0.20 - 0.22 "
Mounting Hole Diameter D (Metric)	5.2 - 5.6 mm
Mounting Hole Diameter D Min (Imperial)	0.20
Mounting Hole Diameter D Max (Imperial)	0.22
Mounting Hole Diameter D Max (Metric)	5.6
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No

Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com